





N=Number of poles

Dim.L	$(N-1) \times 2.5 + 3.0$
Dim.B	$(N-1) \times 2.5$

POLES	TOLERANCE
2P - 3P	-0.15/+0.15



SIGN	DATE	DESCRIPTION	APPROVER
△	03/27`15	Add the safety certification icon	Airy min
△	03/27`15	Update the drawing	Airy min

THIS IS CAD DRAWING, DO NOT REVISE MANUALLY!!!

△Material:

- Item a Terminal housing:LCP (UL94V-0)
- Item b Long solder pin: Copper alloy, Bright Tin plated over Nickel plated
- Item c Short solder pin: Brass, Bright Tin plated over Nickel plated.

△ Electrical UL /cULus (UL1977Standard)

- Voltage rating: 300VAC 300VAC
- Current rating: 6A 3A
- Wire range:
- Solid wire(AWG): 20-26
- Tin Dipped Stranded wire(AWG): 20-26
- Wire strip length: 6-7mm
- Withstanding Voltage: 1.6KV
- Operating temperature: -45°C to +130°C
- Reflow soldering temperature: 260°C/10 Sec Max.
- Safety Approval:
- Critical dimension:

NQ xx 0 1 x 0 xxxx G

△No. OF POLES
02: 2 POLES
03: 3 POLES

△ Color

- 0 Black (RAL9005)
- 1 Natural color
- 8 Grey

G RoHS compliant
(lead<4%)
In copper Alloy

0000: "@" Logo (Standard)
000A: "ANYTEK" Mark
Any special item by
customer request.
please contact sales
department.

ANYTEK

CUSTOMER COPY

ALL RIGHTS RESERVED. REPRODUCTION OR ISSUE TO THIRD PARTIES IN ANY FORM WHATEVER IS NOT PERMITTED WITHOUT WRITTEN AUTHORITY FROM THE PROPRIETOR. PROPERTY OF ANYTEK TECHNOLOGY CO., LTD

TITLE	NQ 2.5mm Series Without flange (SMT)						
PART NO.	NQxx01x0xxxxG			DWG NO.	8NQ0002		
APPROVED	CHECKED	DESIGNED	DRAWN	CUST NO.			
		Airy min 03/27`15	Airy min 03/27`15			UNIT: mm	X. ±0.50
						SCALE: NONE	X.X ±0.30
				SHEET: 01/01	REV.: C		X.XX ±0.10
							X° ±1°