




N = Number of poles
Dim A=Nx5.0
Dim B=(N-1)x5.0

	Dim A	Dim B
2-6p	±0.25	±0.20
7-12p	±0.30	±0.25
13-18p	±0.35	±0.30
19-24p	±0.40	±0.35



SIGN	DATE	DESCRIPTION	APPROVER
△	02/01'07	Soldering temperature is changed from 245°C to 250°C	Marivn
△	03/01'08	BODY 頂部加掩膠.	Tason
△	03/01'08	改溫度.	Tason
△	09/30'10	Add the Fillet	Tason
△	09/30'10	The design is changed	Tason
△	09/30'10	Add the tolerance table	Tason
△	10/12'10	The dimension is changed from 4.0mm to 3.7mm	Tason
△	02/15'11	Add the "tuv" Safety Approval	Tason
△	03/28'12	The dimension is changed from 3.7mm to 4.0mm	Guoxue
△	03/28'12	The dimension 2.5 is added	Guoxue
△	12/10'13	Update the drawing	Guoxue
△	03/11'14	The dimension is changed from 4.0mm to 3.7mm	Guoxue

THIS IS CAD DRAWING, DO NOT REVISE MANUALLY Y!!!

Material

- Item③ Terminal body(metal housing): Brass stamping,Tin plated
- Item⑥ Terminal screw: Steel Zinc plating "+/-" slot type
- Item⑦ Wire guard: Stainless steel
- Item⑧ Insulator (housing): Thermoplastic (UL94V-0)

Electrical UL TUV △

- Voltage rating: 300VAC/250VAC

- Current rating: 8A/12A

- Wire range:

- Solid wire(AWG): 14-26/0.2-2.5mm²

- Stranded wire(AWG): 14-26/0.2-2.5mm²

- Torque: 3.5Lb-In/0.4N.m

- Screw: M2.5

- Wire strip length: 5-6mm

- Withstanding Voltage: 1.6KV

- △ ● Operating temperature: -40°C to +115°C/ -40°C to +105°C

- △ △ ● Soldering temperature: 260°C±5°C/5 Sec

- Safety Approval:

- Critical dimension:

△ T3 xx 04 x 1 xxxx G

		Color		
02	2 POLES	0 Black (RAL9005)	000 0 @ logo	RoHS compliant
03	3 POLES	2 Red (RAL3001/D)	000 A ANY logo	(lead<4%)
...	...	3 Orange(RAL2011/P)	Any special item by	In copper Alloy
24	24 POLES	4 Yellow(RAL1018/A)	customer request,	
		5 Green(RAL6018/T)	please contact sales	
		6 Blue (RAL5015/A)	department.	
		8 Grey(RAL7035/D)		
		C Green(RAL6018/U)		

ANYTEK

CUSTOMER COPY

ALL RIGHTS RESERVED. REPRODUCTION OR ISSUE TO THIRD PARTIES IN ANY FORM WHATEVER IS NOT PERMITTED WITHOUT WRITTEN AUTHORITY FROM THE PROPRIETOR. PROPERTY OF ANYTEK TECHNOLOGY CO., LTD

TITLE		T3 5.0 Series 2-Interlock "+/-" stackable type			
PART NO.	T3xx04x1xxxxG			DWG NO.	8T30101
APPROVED	CHECKED	DESIGNED	DRAWN	CUST NO.	
		Guoxue 2014.03.11	Guoxue 2014.03.11		Tolerance
					X. ±0.50 X.X ±0.30 X.XX ±0.10 X° ±1°
SHEET: 01/01		REV.: 1		UNIT: mm	SCALE: NONE