

REVISIONS					
P	LTR	DESCRIPTION	DATE	DWN	APVD
	E I	REVISED (ECR-16-009129)	23.JUN.'16	SJ	HG
	F	REVISED (ECR-17-008875)	02NOV2017	SJ	KT
	F I	REVISED (ECR-18-009554)	09.JUL'18	EW	YJ
	G	REVISED (ECR-21-002339)	24FEB2021	CH	YJ

D

D

C



C

B



B

A




A



- NOTES.
1. GENERAL TOLERANCE IS ± 0.3 , $\pm 3^\circ$
 2. CONDITION OF DELIVERY
 3. APPLIED CAP ASS'Y P/N : X-1743062-X
APPLIED WIRE COVER P/N : X-1743064-X
 4. APPLIED RECEPTACLE CONTACT P/N : TABLE 1
 5. APPLIED WIRE SEAL P/N : TABLE 2



3D-VIEW
SCALE 1:1





<TABLE 1>

TYPE	Part No.	WIRE SIZE (mm ²)	FINISH
MTII	0-962875-1	0.25 ~ 0.5	CuSn4
	0-962875-3		CuSn4(GOLD)
	0-962876-1	0.5 ~ 1.0	CuSn4
	0-962876-3		CuSn4(GOLD)
JPT	0-927770-3	0.5 ~ 0.85	CuSn4
	2-927770-1		CuSn4(GOLD)
	0-927766-3	1.25 ~ 2.0	CuSn4
	2-927766-1		CuSn4(GOLD)

<TABLE 2>

TYPE	Part No.	WIRE INSULATION DIAMETER(mm)	COLOR
MTII	964971-1	1.2 ~ 1.6	RED
	963530-1	1.7 ~ 1.9	GRAY
	963531-1	CAVITY PLUG	WHITE
	828904-1	1.2 ~ 2.1	BLUE
JPT	828905-1	2.2 ~ 3.0	WHITE
	828922-1	CAVITY PLUG	NATURAL

				ASS'Y P/N			
4	-	SILICONE	INNER SEAL	0-1743059-1	0-1743059-2	0-1743059-2	0-1743059-3
3	GRAY (RAL 7004)	PBT-GF20	LEVER HSG	I	I	-	I
	BLACK (RAL 9011)	PBT-GF20		-	-	I	-
2	DARK GRAY (RAL 7012)	PBT-GF15	MAIN BODY PLUG HSG	-	-	-	I
	BLACK (RAL 9011)	PBT-GF15		-	I	I	-
	NATURAL	PBT-GF15		I	-	-	-
1	BLACK (RAL 9011)	PBT-GF15	FRONT PLUG HSG	I	I	I	I
NO.	COLOR/FINISH	MATERIAL	DESCRIPTION	Q'TY			



SECTION A-A

THIS DRAWING IS A CONTROLLED DOCUMENT.		DWN YD.LEE	TE Connectivity		
		CHK BM JANG			
		APVD CS LEE			
		PRODUCT SPEC			
DIMENSIONS: mm		APPLICATION SPEC		NAME PLUG ASS'Y FOR MTII JPT SLD 36P	
TOLERANCES UNLESS OTHERWISE SPECIFIED:		WEIGHT -		SIZE A2	
0 PLC ±		CUSTOMER DRAWING		CAGE CODE 00779	
1 PLC ±				DRAWING NO C-1743059	
2 PLC ±				RESTRICTED TO -	
3 PLC ±				SCALE 2:1	
4 PLC ±				SHEET 1 OF 1	
ANGLES ±				REV G	
FINISH					
SEE TABLE					