

SIGN	DATE	DESCRIPTION	APPROVER
△	11/25'04	The dimension changed from N×3.81 TO N×3.81+0.80	何恩華
△	11/25'04	Part No. changed from VMxx35x2 to VMxx35x2G	何恩華
△	02/07'06	Part No. changed	Tony
△	08/22'09	Add pad for 2P - 6P .	Kind
THIS IS CAD DRAWING, DO NOT REVISE MANUALLY!!!			

Material

- Item a Clamp: Steel zine plated.
- Item b Terminal screw: Brass Zinc plating “-” slot type
- Item c Female contact: PhBz Tin plated
- Item d Terminal (Up body): Thermoplastic (UL94V-0)
- Item e Terminal (Down body): Thermoplastic (UL94V-0)
- Item f Clampage:Steel Zinc plated

Electrical cULus

- Voltage rating: 300VAC
- Current rating: 10A
- Wire range:
- Solid wire(AWG): 16-28
- Stranded wire(AWG): 16-28
- Torque: 1.7Lb-In
- Screw: M2
- Wire strip length: 6-7mm
- Withstanding Voltage: 1.6KV
- Operating temperature: -40°C to +115°C
- Safety approval: 

POLES		Color		G: Pb<40000ppm	
02 pole	''' '''	0	Black (RAL9005)	0000:	"@"logo
24 pole	''' '''	2	Red (RAL3001/D)	000A:	"ANYTEK"logo
		3	Orange(RAL2011/P)	Any special item by customer request. please contact sales department.	
		4	Yellow(RAL1018/A)		
		5	Green(RAL6018/T)		
		6	Blue (RAL5015/A)		
		8	Grey(RAL7035/D)		

POLE		2	3	4	5	6	7	8	9	10	11	12
Dim.L		8.42	12.23	16.04	19.85	23.66	27.47	31.28	35.09	38.90	42.71	46.52
Dim.P		3.81	7.62	11.43	15.24	19.05	22.86	26.67	30.48	34.29	38.10	41.91
Tol.		±0.20					±0.25					
POLE	13	14	15	16	17	18	19	20	21	22	23	24
Dim.L	50.33	54.14	57.95	61.76	65.57	69.38	73.19	77.00	80.81	84.62	88.43	92.24
Dim.P	45.72	49.53	53.34	57.15	60.96	64.77	68.58	72.39	76.20	80.01	83.82	87.63
Tol.		±0.30					±0.40					

ANYTEK					CUSTOMER COPY				
ALL RIGHTS RESERVED. REPRODUCTION OR ISSUE TO THIRD PARTIES IN ANY FORM WHATEVER IS NOT PERMITTED WITHOUT WRITTEN AUTHORITY FROM THE PROPRIETOR. PROPERTY OF ANYTEK TECHNOLOGY CO., LTD									
TITLE		VM 3.81mm W/O Flange Series							
PART NO.		VMxx35x0xxxxG				DWG NO.		8VM0201	
APPROVED		CHECKED	DESIGNED	DRAWN	CUST NO.		Tolerance		
			Kind 2009.08.22	Kind 2009.08.22			UNIT: mm		X. ±0.50
							SCALE: NONE		X.X ±0.30
					SHEET: 01/01		REV.: D		X.XX ±0.10
									X° ±1°
5			6				7		