



P.C.B LAYOUT

(N= Number of poles)

DIM		TOL		
		2P-5P	6P-10P	11P-16P
Dim L	(N-1)×7.5+18	±0.15	±0.25	±0.35
Dim A	(N-1)×7.5+5.52	±0.15	±0.25	±0.35
Dim B	(N-1)×7.5	±0.15	±0.25	±0.35
Dim C	(N-1)×7.5	±0.15	±0.25	±0.35
Dim D	(N-1)×7.5+12.2	±0.15	±0.25	±0.35

SIGN	DATE	DESCRIPTION	APPROVER
△	01/15'10	The design is changed	Jacke
△	01/15'10	The design is changed from the round hole to hexagonal hole	Jacke
△	01/15'10	Add cULus standard	Jacke
△	03/31'10	Add the 2p mark	Jacke
△	04/28'12	Flange Nut is changed	Guoxue
△	04/28'12	Add the cutaway view	Guoxue
△	04/28'12	The dimensions are added	Guoxue

THIS IS CAD DRAWING, DO NOT REVISE MANUALLY!!!

Materials

- Item a Terminal body: Thermoplastic (UL94V-0)
- Item b Terminal Cover: Thermoplastic (UL94V-0)
- Item c Female contact : PhBz(CuSn), Tin plated
- Item d With flange Nut : Brass M 2.5

Electrical

- Voltage rating: 300VAC
- Current rating: 10A
- Withstanding Voltage: 1.6kv
- Operating temperature: -40°C to +115°C
- Soldering temperature: 250°C±10°C/5 Sec
- Safety Approval: cULus

- Critical dimension:

V7 xx A 2 x 1 xxxx G

No. OF POLES
02 2 POLES
03 3 POLES
...
16 16 POLES

Color

- 0 Black (RAL9005)
- 2 Red (RAL3001/D)
- 3 Orange(RAL2011/P)
- 4 Yellow(RAL1018/A)
- 5 Green(RAL6018/T)
- 6 Blue (RAL5015/A)
- 8 Grey(RAL7035/D)

G RoHS compliant
(lead<4%)
In copper Alloy

0000: "@" Logo (Standard)
000A: "ANYTEK" Mark
Any special item by
customer request.
please contact sales
department.

ANYTEK

INSPECTION COPY

ALL RIGHTS RESERVED. REPRODUCTION OR ISSUE TO THIRD PARTIES IN ANY FORM WHATEVER IS NOT PERMITTED WITHOUT WRITTEN AUTHORITY FROM THE PROPRIETOR. PROPERTY OF ANYTEK TECHNOLOGY CO., LTD

TITLE		V7 7.5 Series Right-angle (2P~16P)W/F				
PART NO.	V7xxA2x1xxxxG			DWG NO.	8V70404	
APPROVED	CHECKED	DESIGNED	DRAWN	CUST NO.	Tolerance	
		Guoxue 2012.04.28	Guoxue 2012.04.28		UNIT: mm	X. ±0.5
					SCALE: 1/4	X.X ±0.3
				SHEET: 01/01	REV: E	X.XX ±0.1
						X° ±1°