





SIGN	DATE	DESCRIPTION	APPROVER
△			
THIS IS CAD DRAWING, DO NOT REVISE MANUALLY!!!			

- Material
- Item ① Terminal body: Thermoplastic (UL94V-0)
 - Item ② Spring clamp of short : Brass Tin plated.
 - Item ③ Spring clamp of long : Brass Tin plated.
 - Item ④ Spring clamp: Stainless steel
 - Item ⑤ Terminal cover : Thermoplastic (UL94V-0)
 - Item ⑥ Pad board: Thermoplastic (UL94V-0)
- Electrical: cULus
- Voltage rating: 300V
 - Current rating: 10A
 - Wire range:
 - Solid wire(AWG): 12-28
 - Stranded wire(AWG): 12-28
 - Wire strip length: 5-6mm
 - Withstanding Voltage: 1.6KV
 - Operating temperature: -40°C to +115°C
 - Soldering temperature: 250°C±10°C/5 Sec
- △ ● Safety Approval:  US

HQ xx 4 0 x 1 xxxx G

No. OF POLES

- 02: 2×1 POLES
- 04: 2×2 POLES
- 24: 2×12 POLES

COLOR

- 0: BLACK
- 5: GREEN (RAL 6018/T)
- 6: BLUE
- 8: GREY (RAL 7004/P)

G: Pb<40000ppm

0000: "@" Logo (Standard)

000A: "ANYTEK" Mark

Any special item by customer request. please contact sales department.

PCB Layout											
POLE		2x2	2x3	2x4	2x5	2x6	2x7	2x8	2x9	2x10	2x12
A		16.24	26.40	36.56	46.72	56.88	67.04	77.20	87.36	97.52	107.68
B		10.16	20.32	30.48	40.64	50.80	60.96	71.12	81.28	91.44	101.60
Tol.		±0.10					±0.15				

ANYTEK

TITLE

HQ 10.16mm Series (Solder pins staggered by half the pin spacing)

PART NO.

HQxx40x1xxxxG

APPROVED

CHECKED

DESIGNED

DRAWN

CUST NO.

Runner

2010.05.13

Runner

2010.05.13



SHEET: 01/01

CUSTOMER COPY

ALL RIGHTS RESERVED. REPRODUCTION OR ISSUE TO THIRD PARTIES IN ANY FORM WHATSOEVER IS NOT PERMITTED WITHOUT WRITTEN AUTHORITY FROM THE PROPRIETOR. PROPERTY OF ANYTEK TECHNOLOGY CO., LTD

DWG NO.

8HQ0103

Tolerance

X. ±0.50

X.X ±0.30

X.XX ±0.10

X° ±1°

UNIT: mm

SCALE: NONE

REV.: B