



1 3

△₃ Material

- Item a Clamp: Brass (CuZn) Ni plated
- Item b Female contact :PbBz(CuSn) Tin plated
- Item c Terminal screw:Steel Zinc plating “-” slot type
- Item d Terminal (housing):Thermoplastic (UL94V-0)
- Item e Terminal cover:Thermoplastic (UL94V-0)
- Item f With flange screw: Steel Zinc plating “+/-” slot type M2.5

Electrical cULus

- Voltage rating:300V
- Current rating:8A
- Wire range:
- Solid wire(AWG):16-28
- Stranded wire(AWG):16-28
- Torque(Lb-In):1.7
- Screw:M2
- Wire strip length:6-7mm
- Withstanding Voltage:1.6KV
- Operating temperature:-40℃ to +115℃
- Safety Approval:

VD xx 31 x 2 xxxx G

- | | | |
|----------|-------------------|---|
| 3 | Solid Block | G RoHS compliant
(lead<4%)
In copper Alloy |
| 02 | 2 POLES | |
| 03 | 3 POLES | |
| ... | ... | |
| 24 | 24 POLES | |
| 0 | Black (RAL9005) | 0000 Standard @ Logo |
| 2 | Red (RAL3001/D) | 000A Standard ANY Logo |
| 3 | Orange(RAL2011/P) | 0091 Standard ANY Logo |
| 4 | Yellow(RAL1018/A) | Any special item by customer request,
please contact sales department. |
| 5 | Green(RAL6018/T) | |
| 6 | Blue (RAL5015/A) | |
| 8 | Grey(RAL7035/D) | |
| 9 | White(RAL1102) | |
| C | Green(RAL6018/U) | |

ANYTEK

CUSTOMER COPY

ALL RIGHTS RESERVED. REPRODUCTION OR ISSUE TO THIRD PARTIES IN ANY FORM WHATEVER IS NOT PERMITTED WITHOUT WRITTEN AUTHORITY FROM THE PROPRIETOR. PROPERTY OF ANYTEK TECHNOLOGY CO. LTD

TITLE		VD-3.81 SERIES (with flange)			
PART NO.	VDxx31x2xxxxG			DWG NO.	8VD0002
APPROVED	CHECKED	DESIGNED	DRAWN	CUST NO.	Tolerance
			Ji long 2014.06.10		UNIT: mm X. ±0.50 X.X ±0.30 X.XX ±0.10
				SHEET: 01/01	REV: E X° ±1°