


Dimension A&B



DIM A	N×5.0
DIM B	(N-1)×5.0

N=Number of contacts

Poles	A&B Tolerance
2P-8P	±0.15
9P-14P	±0.25
15P-20P	±0.35
21P-24P	±0.40



N=Number of contacts



RECOMMENDED PCB LAYOUT

SIGN	DATE	DESCRIPTION	APPROVER
△	2/10'06	Part NO is Changed	xionghaitao
△	2/10'06	Design is Changed	xionghaitao

Material

- Item① Clamp : Brass , Ni plated
- Item② Terminal screw: Steel , Zinc plating "- slot type
- Item③ Wire guard solder pin : Brass , Tin plated
- Item④ Terminal housing : Thermoplastic (UL94V-0)

Electrical UL

- Voltage rating: 300VAC
- Current rating: 10A
- Wire range:
- Solid wire(AWG): 12-24
- Stranded wire(AWG): 12-24
- Torque(Lb-In): 3.5
- Screw: M2.5
- Wire strip length: 6-7mm
- Withstanding Voltage: 1.6KV
- Operating temperature: -40°C to +115°C
- Soldering temperature: 250°C±10°C/5 Sec
- Safety Approval Deta:

T2 xx 0 1 x 0 xxxx G			
02 2 CONTACTS	0 Black	0000:"@Logo (Standard)	RoHS
03 3 CONTACTS	5 Green	000A:"ANYTEK"Logo	Pb<40,000ppm
...	(RAL 6018/T)	Any special item by	
24 24 CONTACTS	6 Blue	customer request,	
	8 Grey	please contact sales	
	(RAL 7035/D)	department.	

ANYTEK

CUSTOMER COPY

ALL RIGHTS RESERVED. REPRODUCTION OR ISSUE TO THIRD PARTIES IN ANY FORM WHATEVER IS NOT PERMITTED WITHOUT WRITTEN AUTHORITY FROM THE PROPRIETOR. PROPERTY OF ANYTEK TECHNOLOGY CO., LTD

TITLE		T2 - 5.0mm series 2P-24P (Stackable)					
PART NO.		T2xx01x0xxxxG 			DWG NO.	8T20001	
APPROVED	CHECKED	DESIGNED	DRAWN	CUST NO.		Tolerance	
		Aaron 2009.11.14	xionghaitao 2006.01.23			UNIT: mm	X. ±0.50
						SCALE: NONE	X.X ±0.30
				SHEET: 01/01		REV.: C	X.XX ±0.10
						X° ±1°	