



1707




1707-0-19-XX-30-XX-10-0
Press-fit in .061 mounting hole

0240




0240-0-15-XX-30-XX-04-0
Press-fit in .059 mounting hole

0307




0307-0-15-XX-30-XX-04-0
Press-fit in .059 mounting hole

1753



1753-0-15-XX-30-XX-04-0
Press-fit in .057 mounting hole


1705/1706/1762



17XX-0-15-XX-35-XX-04-0
Press-fit in .057 mounting hole

Basic Part Number	Height A
1705-0	.165
1706-0	.218
1762-0	.300


0672



0672-X-15-XX-30-XX-10-0
Swage mount in .049 hole

Basic Part Number	Board Thickness	Length V
0672-1	.031	.052
0672-2	.062	.084
0672-3	.094	.115
0672-4	.125	.146


1024/1104



1XX4-0-18-XX-30-XX-10-0
Press-fit in .059 mounting hole


Basic Part Number	Length A
1024-0	.290
1104-0	.450

0498



0498-0-15-XX-35-XX-04-0
Press-fit in .057 mounting hole

8131



8131-0-15-XX-30-XX-10-0
Press-fit in .057 mounting hole

SPECIFICATIONS

SHELL MATERIAL:
Brass Alloy 360, 1/2 Hard

CONTACT MATERIAL:
Beryllium Copper Alloy 172, HT

DIMENSION IN INCHES
TOLERANCES ON:
LENGTHS: ±.005
DIAMETERS: ±.002
ANGLES: ± 2°

ORDER CODE: XXXX - X - 1X - XX - XX - XX - XX - 0

BASIC PART #
SPECIFY SHELL FINISH:
01 200μ" TIN/LEAD OVER NICKEL
15 10μ" GOLD OVER NICKEL

SPECIFY CONTACT FINISH:
02 200μ" TIN/LEAD OVER NICKEL
14 10μ" GOLD OVER NICKEL
27 30μ" GOLD OVER NICKEL

SELECT CONTACT

#30 or #35 CONTACT (DATA ON PAGES 208 & 209)