




RECOMMENDED PCB LAYOUT

N = Number of poles
Dim A=Nx5.0
Dim B=(N-1)x5.0

	Dim A	Dim B
2-6p	±0.15	±0.10
7-12p	±0.20	±0.20
13-18p	±0.30	±0.25
19-24p	±0.40	±0.30



SIGN	DATE	DESCRIPTION	APPROVER
△	02/09'06	Part No. is changed.	Marvin
△	06/22'06	Safety is changed from UL 250V/16A to cULus 300V/15A	Marvin
△	08/01'06	cULus Solid wire and Stranded wire is changed.	Marvin
△	04/03'10	Part No. is changed.	Tason
△	09/27'10	Wire range is changed from 0.75-1.5mm ² to 0.5-1.5mm ²	Tason
△	05/11'11	The dimension is changed from 9.9mm to 10.0mm	Tason
△	05/11'11	Change here	Tason
△	05/11'11	The CSA spec is removed	Tason
THIS IS CAD DRAWING, DO NOT REVISE MANUALLY!!!			

Material

- Item② Terminal body: Brass(CuZn),Tin plated
- Item③ Terminal screw: Steel Zinc plating "-" slot type
- Item④ Wire guard: Stainless steel
- Item⑤ Terminal housing:Thermoplastic (UL94 V-0)

Electrical cULus/VDE

- Voltage rating: 300VAC/250VAC
- Current rating: 15A/17.5A
- Wire range:0.5-1.5mm²
- Solid wire(AWG): 14-22/14-22
- Stranded wire(AWG): 14-22/14-22
- Torque: 2.6Lb-In/0.4Nm
- Screw: M2.6
- Wire strip length: 5-6mm
- Withstanding Voltage: 1.6KV/2KV
- Operating temperature: -40°C to +115°C
- Soldering temperature: 250°C±10°C/5 Sec
- SAFETY APPROVAL DETA: cULus VDE △
- Critical dimension:▽

TC xx 0 3 x x xxxx G △

POLES
02 02 CONTACTS
03 03 CONTACTS
...
24 24 CONTACTS

COLOR
0 BLACK
5 GREEN(RAL6018/T)
6 BLUE
8 GREY(RAL7035/D)
C GREEN (RAL6018/U)

DIM C Length
0 4.4mm
1 3.8mm
2 3.5mm
3 2.9mm

000 0 Standard @ logo
000 A Standard ANY logo
Any special item by
customer request,
please contact sales
department.

ANYTEK

CUSTOMER COPY

ALL RIGHTS RESERVED. REPRODUCTION OR ISSUE TO THIRD PARTIES IN ANY FORM WHATSOEVER IS NOT PERMITTED WITHOUT WRITTEN AUTHORITY FROM THE PROPRIETOR. PROPERTY OF ANYTEK TECHNOLOGY CO., LTD

TITLE		TC-5.0 Series 2-Interlock			
PART NO.	TCxx03xxxxxxG △			DWG NO.	8TC0061
APPROVED	CHECKED	DESIGNED	DRAWN	CUST NO.	
		Tason 2011.05.11	Tason 2010.04.03		
SHEET: 01/01				UNIT: mm	X. ±0.50
				SCALE: NONE	X.X ±0.30
				REV.: D	X.XX ±0.10
					X° ±1°