







P.C.B LAYOUT
Top view

N = Number of poles

Dim L = N x 5.00 + 1.5
Dim B = (N - 1) x 5.00

POLES	Dim L	Dim B
1p	±0.1	±0.15
2p-6p	±0.2	±0.15
7p-12p	±0.3	±0.25
13p-18p	±0.4	±0.35
19p-24p	±0.45	±0.4

SIGN	DATE	DESCRIPTION	APPROVER
Δ	1/31/07	The soldering temperature from 245° to 250°	Aaron
Δ	05/28/13	change the structure	Da cheng
Δ	05/28/13	update the drawing	Da cheng
Δ			
Δ			

THIS IS CAD DRAWING, DO NOT REVISE MANUALLY!!!

Material

- Item ① Insulator body: Thermoplastic (UL94V-0)
- Item ② Insulating cover: Thermoplastic (UL94V-0)
- Item ③ Contact pin: Brass, Tin plated
- Item ④ Wire guard: Stainless steel

Electrical:

- Voltage rating: 250V
- Current rating: 8A
- Wire range:
- Solid wire(AWG): 12-28
- Stranded wire(AWG): 12-28
- Wire strip length: 8-9mm
- Withstanding Voltage: 15KV
- Operating temperature: -40°C to +115°C
- Safety Approval: cULus
- Critical dimension: ∇

HIM XX 70 x 1 xxxx G

No. OF POLES

- 01: 1 POLES
- 02: 2 POLES

24: 24 POLES

Δ COLOR

- 0: Black (RAL9005)
- 2: Red (RAL3001/D)

3: Orange(RAL2011/P)

4: Yellow(RAL1018/A)

5: Green(RAL6018/T)

6: Blue (RAL5015/A)

8: Grey(RAL7004/P)

9: White(RAL1102)

C: Multiple colors

Δ RoHS compliant
(lead<4%)
In copper Alloy

0000 Standard @ Logo

000A Standard ANY Logo

Any special item by

customer request,

please contact sales

department.

ANYTEK

CUSTOMER COPY

ALL RIGHTS RESERVED. REPRODUCTION OR ISSUE TO THIRD PARTIES IN ANY FORM WHATSOEVER IS NOT PERMITTED WITHOUT WRITTEN AUTHORITY FROM THE PROPRIETOR. PROPERTY OF ANYTEK TECHNOLOGY CO., LTD

TITLE	HM 5.0mm Series Press fit Type		DWG NO.	8HM0002	
PART NO.	HMxx70x1xxxxG		CUST NO.		
APPROVED	CHECKED	DESIGNED	DRAWN		
	Da cheng 2013.05.28	Da cheng 2013.05.28			
			SHEET: 01/01	REV: F	

UNIT:	mm	Tolerance	±0.50
SCALE:	NONE		±0.30
			±0.10
			±1°