

UUN

Chip Type, Bi-Polarized,
Higher Capacitance Range

For SMD



Bi-polarized

Anti-Solvent
Feature

- Chip Type, higher capacitance in larger case sizes ($\phi 12.5$, $\phi 16$, $\phi 18$)
- Designed for surface mounting on high density PC board.
- Bi-polarized series for operations over wide temperature range of -55 to $+105^{\circ}\text{C}$.
- Applicable to automatic mounting machine fed with carrier tape.
- Compliant to the RoHS directive (2011/65/EU, (EU)2015/863).

UUN

Bi-polarized

UUJ




■ Specifications

Item	Performance Characteristics									
Category Temperature Range	-55 to +105°C									
Rated Voltage Range	6.3 to 100V									
Rated Capacitance Range	22 to 3300μF									
Capacitance Tolerance	±20% at 120Hz, 20°C									
Leakage Current ※	After 1 minute's application of rated voltage at 20°C, leakage current is not more than 0.03CV or 4 (μA), whichever is greater.									
Tangent of loss angle (tan δ)	Measurement frequency : 120Hz at 20°C									
	Rated voltage (V)	6.3	10	16	25	35	50	63	100	
	tan δ (max.)	0.26	0.22	0.18	0.16	0.14	0.12	0.10	0.09	
	For capacitance of more than 1000μF, add 0.02 for every increase of 1000μF.									
Stability at Low Temperature	Measurement frequency: 120Hz									
	Rated voltage (V)	6.3	10	16	25	35	50	63	100	
	Impedance ratio (max.)	Z(-25°C) / Z(+20°C)	5	4	3	2	2	2	2	
		Z(-40°C) / Z(+20°C)	10	8	6	4	3	3	3	
Endurance	The specifications listed at right shall be met when the capacitors are restored to 20°C after the rated voltage is applied for 2000 hours at 105°C with the polarity inverted every 250 hours.					Capacitance change		Within ±20% of the initial capacitance value		
						tan δ		200% or less than the initial specified value		
						Leakage current		Less than or equal to the initial specified value		
Shelf Life	After storing the capacitors under no load at 105°C for 1000 hours and then performing voltage treatment based on JIS C 5101-4 clause 4.1 at 20°C, they shall meet the specified values for the endurance characteristics listed above.									
Marking	Black print on the case top.									

※ I : Leakage Current (μA), C : Rated Capacitance (μF), V : Rated Voltage (V)


■ Chip Type



(mm)

φD	12.5×13.5	12.5×16	16×16.5	16×21.5	18×16.5	18×21.5
A	5.15	5.15	5.65	5.65	6.65	6.65
B	13.6	13.6	17.1	17.1	19.1	19.1
C	13.6	13.6	17.1	17.1	19.1	19.1
E	(3.3)	(3.3)	(5.8)	(5.8)	(5.8)	(5.8)
L	13.5	16.0	16.5	21.5	16.5	21.5
H	1.0 to 1.4	1.0 to 1.4	1.0 to 1.4	1.0 to 1.4	1.0 to 1.4	1.0 to 1.4

Please contact us for the dimensions for NQ.

Type numbering system (Example : 50V 330 μF)

Code	Remarks
NJ	Standard Style
NQ	Products which are scheduled to be discontinued. Not recommended for new designs.

※ There are also some products that can be manufactured as vibration resistant products.

● Frequency coefficient of rated ripple current

Cap. (μF) \ Frequency	50 Hz	120 Hz	300 Hz	1 kHz	10 kHz or more
22 to 47	0.75	1.00	1.35	1.57	2.00
100 to 470	0.80	1.00	1.23	1.34	1.50
1000 to 3300	0.85	1.00	1.10	1.13	1.15

● Dimension table in next page.

UUN

■ Dimensions

Rated Voltage (V) (code)	Rated Capacitance (μ F)	Case Size ϕ D $\times$ L (mm)	$\tan \delta$	Leakage Current (μ A) (at 20°C after 1 minute)	Rated Ripple (mArms) (105°C/120Hz)	Part Number
6.3 (0J)	470	12.5 $\times$ 13.5	0.26	88.83	270	UUN0J471M NJ1MS
	1000	12.5 $\times$ 16	0.26	189	500	UUN0J102M NJ1MS
	2200	18 $\times$ 16.5	0.28	415.8	740	UUN0J222M NJ1MS
	2200	16 $\times$ 21.5	0.28	415.8	740	UUN0J222M NJ6MS
	3300	18 $\times$ 21.5	0.30	623.7	920	UUN0J332M NJ1MS
10 (1A)	470	12.5 $\times$ 13.5	0.22	141	340	UUN1A471M NJ1MS
	1000	16 $\times$ 16.5	0.22	300	600	UUN1A102M NJ1MS
	2200	18 $\times$ 21.5	0.24	660	830	UUN1A222M NJ1MS
16 (1C)	330	12.5 $\times$ 13.5	0.18	158.4	310	UUN1C331M NJ1MS
	470	16 $\times$ 16.5	0.18	225.6	420	UUN1C471M NJ1MS
	1000	18 $\times$ 16.5	0.18	480	670	UUN1C102M NJ1MS
	1000	16 $\times$ 21.5	0.18	480	670	UUN1C102M NJ6MS
25 (1E)	220	12.5 $\times$ 13.5	0.16	165	270	UUN1E221M NJ1MS
	330	16 $\times$ 16.5	0.16	247.5	370	UUN1E331M NJ1MS
	470	16 $\times$ 16.5	0.16	352.5	490	UUN1E471M NJ1MS
	1000	18 $\times$ 21.5	0.16	750	780	UUN1E102M NJ1MS
35 (1V)	100	12.5 $\times$ 13.5	0.14	105	180	UUN1V101M NJ1MS
	220	16 $\times$ 16.5	0.14	231	330	UUN1V221M NJ1MS
	330	18 $\times$ 16.5	0.14	346.5	450	UUN1V331M NJ1MS
	330	16 $\times$ 21.5	0.14	346.5	450	UUN1V331M NJ6MS
	470	18 $\times$ 21.5	0.14	493.5	590	UUN1V471M NJ1MS
50 (1H)	47	12.5 $\times$ 13.5	0.12	70.5	130	UUN1H470M NJ1MS
	100	12.5 $\times$ 16	0.12	150	230	UUN1H101M NJ1MS
	220	18 $\times$ 16.5	0.12	330	400	UUN1H221M NJ1MS
	220	16 $\times$ 21.5	0.12	330	400	UUN1H221M NJ6MS
	330	18 $\times$ 21.5	0.12	495	540	UUN1H331M NJ1MS
	470	18 $\times$ 21.5	0.12	705	640	UUN1H471M NJ6MS
63 (1J)	47	12.5 $\times$ 13.5	0.10	88.83	140	UUN1J470M NJ1MS
	100	16 $\times$ 16.5	0.10	189	270	UUN1J101M NJ1MS
	220	18 $\times$ 21.5	0.10	415.8	440	UUN1J221M NJ1MS
	330	18 $\times$ 21.5	0.10	623.7	590	UUN1J331M NJ6MS
100 (2A)	22	12.5 $\times$ 13.5	0.09	66	100	UUN2A220M NJ1MS
	33	12.5 $\times$ 16	0.09	99	150	UUN2A330M NJ1MS
	47	16 $\times$ 16.5	0.09	141	180	UUN2A470M NJ1MS
	100	18 $\times$ 21.5	0.09	300	310	UUN2A101M NJ1MS

• For taping specifications, recommended land size/soldering by reflow and minimum order quantity, please refer to the Guidelines for Aluminum Electrolytic Capacitors.