

SIGN	DATE	DESCRIPTION	APPROVER
△			
THIS IS CAD DRAWING, DO NOT REVISE MANUALLY!!!			

Material

- Item ③ Long contact pin: Copper ,Tin plated
- Item ④ Short contact pin : Copper ,Tin plated
- Item ⑤ Terminal (housing): Thermoplastic (UL94V-0)

Electrical

- Voltage rating: 300VAC
- Current rating: 10A
- Withstanding Voltage: 1.6KV
- Operating temperature: -40°C to +115°C
- Soldering temperature: 260°C±5°C/5 Sec
- Safety Approval: 
- Critical dimension: 

VF xx 3 1 x 0 xxxx G

No. OF POLES
34: 2x17 POLES
38: 2x19 POLES

Color
0 Black (RAL9005)
2 Red (RAL3001/D)
3 Orange(RAL2011/P)
4 Yellow(RAL1018/A)
5 Green(RAL6018/T)
6 Blue (RAL5015/A)
8 Grey(RAL7035/D)
9 White(RAL1102)
C Green(RAL6018/U)



G RoHS compliant
(lead<4%)
In copper Alloy
0000: "®" Logo (Standard)
000A: "ANYTEK" Mark
Any special item by
customer request.
please contact sales
department.

ANYTEK



CUSTOMER COPY

ALL RIGHTS RESERVED. REPRODUCTION OR ISSUE TO THIRD PARTIES IN ANY FORM WHATEVER IS NOT PERMITTED WITHOUT WRITTEN AUTHORITY FROM THE PROPRIETOR. PROPERTY OF ANYTEK TECHNOLOGY CO., LTD

TITLE		VF-3.81 Series Vertical without flange			
PART NO.	VFxx31x0xxxxG			DWG NO.	8VF0208
APPROVED	CHECKED	DESIGNED	DRAWN	CUST NO.	
		Evan 11/15`14	Evan 11/15`14		UNIT: mm
					SCALE: NONE
SHEET: 01/01				REV.: B	
				X.	±0.50
				X.X	±0.30
				X.XX	±0.10
				X°	±1°



RECOMMENDED PCB LAYOUT
TOP VIEW



N = Number of poles

Dim L=(N/2)x3.81+0.79 N= NUMBER OF POLES

Dim B=((N/2)-1)x3.81

Dim C=((N/2)-1)x3.81

Dim D=((N/2)-1)x3.81

Dim E=(N/2)x3.81+1.39

Poles	Tolerance		
2x17P	±0.30	 0.60	 0.55
2x19P	±0.30	 0.65	 0.55