



REVISIONS					
P	LTR	DESCRIPTION	DATE	DWN	APVD
	A	REL PER ECO-18-015319	18SEP2018	JM	RB
	A1	REV PER ECO-18-016694	18OCT2018	JM	RB

D


D



2320936-2
SCALE 2:1
KEY B



2320936-3
SCALE 2:1
KEY C




2320936-4
SCALE 2:1
KEY D


- 1 MATERIAL: 15% FIBERGLASS REINFORCED PBT
COLOR: GRAY
- 2 MATERIAL: 15% FIBERGLASS REINFORCED PBT
COLOR: (SEE TABLE)
- 3 MATERIAL: SILICONE
COLOR: RUST
- 4 MATERIAL: 15% FIBERGLASS REINFORCED PBT
COLOR: ORANGE
- 5 MATERIAL: SILICONE
COLOR: TAN

C

C



2320936-1 SHOWN
KEY A




SECTION A-A

6. RECOMMENDED WIRE DIAMETER RANGE IS 1.30 TO 2.54mm.
7. RECOMMENDED BACKSHELLS:
STRAIGHT EXIT:
A. 2292801-1 SMOOTH WIRE EXIT
B. 2292801-2 NC20/NW17 CONDUIT WIRE EXIT
C. 2292801-3 NC16/NW13 CONDUIT WIRE EXIT
90° EXIT:
D. 2302494-1 SMOOTH WIRE EXIT
E. 2302494-2 NC20/NW17 CONDUIT WIRE EXIT
F. 2302494-3 NC16/NW13 CONDUIT WIRE EXIT
8. RECOMMENDED SEAL PLUG: 776363-1
9. MATING CONNECTOR: 2320930-X.


B

B



A

A



SECTION A-A

D	ORANGE	2320936-4
C	PURPLE	2320936-3
B	BLUE	2320936-2
A	TAN	2320936-1
KEY	TPA COLOR	PART NUMBER

THIS DRAWING IS A CONTROLLED DOCUMENT.		DWN J. MCNEAL 18SEP2018	TE Connectivity			
		CHK R. BALTER 18SEP2018				
		APVD R. BALTER 18SEP2018	NAME PLUG ASSEMBLY, 8 POSITION REDUCED DIA SEAL, HIGH TEMP, AMPSEAL 16			
		PRODUCT SPEC 108-2184				
		APPLICATION SPEC 114-13065	SIZE A2 CAGE CODE - DRAWING NO C-2320936 RESTRICTED TO			
		WEIGHT 16±1g				
MATERIAL -		CUSTOMER DRAWING	SCALE 2:1 SHEET 1 OF 1 REV A1			