







N = Number of poles
 Dim L = $N \times 7.62 + 1.5$
 Dim P = $(N - 1) \times 7.62$

	Dim L	Dim P
2-4p	±0.25	±0.20
5-7p	±0.30	±0.25
8-11p	±0.35	±0.30
12-16p	±0.40	±0.35

SIGN	DATE	DESCRIPTION	APPROVER
△			
THIS IS CAD DRAWING, DO NOT REVISE MANUALLY!!!			

Material

- Item a Terminal body: Thermoplastic (UL94V-0)
- Item b Terminal cover: Thermoplastic (UL94V-0)
- Item c Terminal screw: Steel Zinc plating "- " slot type
- Item d Clampage: Steel, Zinc plated
- Item e Clamp: Steel, Zinc plating
- Item f Solder pin: Copper, Tin plated

Electrical

- Voltage rating: 300VAC
- Current rating: 30A
- Wire range:
- Solid wire(AWG): 10-24
- Stranded wire(AWG): 10-24
- Torque(Lb-In): 4.3
- Screw: M3
- Wire strip length: 15-16mm
- Withstanding Voltage: 1.6KV
- Operating temperature: -40°C to +115°C
- Soldering temperature: 250°C±10°C/5 Sec
- Safety Approval:
- Critical dimension:

KH xx15 x 0 xxxx G		G RoHS compliant (lead<4%) In copper Alloy
02 2 CONTACTS	0 Black (RAL9005)	
03 3 CONTACTS	2 Red (RAL3001/D)	0000 Standard @ Logo 000A Standard ANY Logo Any special item by customer request, please contact sales department.
... ..	3 Orange(RAL2011/P)	
16 16 CONTACTS	4 Yellow(RAL1018/A)	
	5 Green(RAL6018/T)	
	6 Blue (RAL5015/A)	
	8 Grey(RAL7035/D)	

ANYTEK				CUSTOMER COPY			
				ALL RIGHTS RESERVED. REPRODUCTION OR ISSUE TO THIRD PARTIES IN ANY FORM WHATEVER IS NOT PERMITTED WITHOUT WRITTEN AUTHORITY FROM THE PROPRIETOR. PROPERTY OF ANYTEK TECHNOLOGY CO., LTD			
TITLE		KH 7.62 Series 90D Wire inlet					
PART NO.		KHxx15x0xxxxG		DWG NO.		8KH0102	
APPROVED		CHECKED	DESIGNED	DRAWN	CUST NO.		Tolerance
				Chen Bo 12/30 '11			X. ±0.50
					UNIT: mm		X.X ±0.30
					SCALE: NONE		X.XX ±0.10
					REV.: B		X° ±1°
					SHEET: 01/01		