






N = Number of poles
Dim A=Nx9.5+1.5
Dim B=(N-1)x9.5

Poles	Tol.	Dim A&B
2-4p		±0.20
5-8p		±0.25
9-16p		±0.35
17-23p		±0.40
24-30p		±0.50

SIGN	DATE	DESCRIPTION	APPROVER
△	10/20'08	Add APPROVAL: : CQC	Kind
△	4/17'09	Explanation changed	Eris
△	06/04`11	Critical dimension is changed.	Tason
△	06/04`11	The Wire Range is changed from 20-14AWG to 22-14AWG	Tason
△	06/04`11	The tolerance table is changed.	Tason
△	06/16`11	The dimension is changed from 5.55 to 5.5	Tason
△	06/16`11	The dimension is changed from 1.6 to 1.5	Tason
△	11/10'12	Change the screw plating specification	Jacky
△	12/23'13	Change the withatand voltage , current,Screw Torque.	Guoxue

THIS IS CAD DRAWING, DO NOT REVISE MANUALLY!!!

MATERIALS ELECTRICAL	cULus	CQC
△2 RATED VOLTAGE & CURRENT:	300 V, 30A	/ 300V 24A △9
WITHSTAND VOLTAGE:	AC2500V/min	△9
INSULATION RESISTANCE:	1000 MΩ	OR MORE AT DC 500 V
OPERATING TEMPERATURE RANG:	-40 °C ~ +115 °C	
SCREW TORQUE VALUE:	10.54 Lb-In.	/ 0.8Nm △9
△2 WIRE RANGE:	22 - 10 AWG	/ 22-14 AWG △4
1) MOLDED PARTS:	Thermoplastic, UL 94 V-0 BLACK	
2) TERMINAL:	BRASS, 0.8t, Tin PLATED	
△8 3) TERMINAL SCREWS:	STEEL, M3.5	
△9 Critical dimension:		
△1 APPROVAL:	cULus	CQC
PART NO:	YK 447 xx 0 x x 00G	G:RoHS compliant (lead<4%)in copper alloy
NO. OF POLES	02: 2 POLES 03: 3 POLES 04: 4 POLES :	MARK 0: "@ " MARK 1: "ANY " MARK
30: 30 POLES		
△8 0: TERMINAL & SCREW: G/F		
△8 1: TERMINAL: G/F, SCREW: Zinc		
2: TERMINAL: Sn, SCREW: G/F		
△8 3: TERMINAL: Sn, SCREW: Zinc		

ANYTEK

CUSTOMER COPY

ALL RIGHTS RESERVED. REPRODUCTION OR ISSUE TO THIRD PARTIES IN ANY FORM WHATEVER IS NOT PERMITTED WITHOUT WRITTEN AUTHORITY FROM THE PROPRIETOR. PROPERTY OF ANYTEK TECHNOLOGY CO., LTD

TITLE		YK-447 Series								
PART NO.		YK447xx0xx00G			DWG NO.		8YK0001-447			
APPROVED		CHECKED	DESIGNED	DRAWN	CUST NO.				Tolerance	
			Guoxue 2014.01.07	Guoxue 2014.01.07			UNIT: mm		X.	±0.50
							SCALE: NONE		X.X	±0.30
							REV.: H		X.XX	±0.10
					SHEET: 01/01				X°	±1°