




P.C.B LAYOUT



SECTION A-A

N = Number of poles  
 Dim A=Nx5.0+3.2  
 Dim B=Nx5.0+0.7  
 Dim C=(N-1)x5.0

|        | Dim A | Dim B       | Dim C |
|--------|-------|-------------|-------|
| 2-6p   | ±0.20 | +0.15<br>-0 | ±0.20 |
| 6-12p  | ±0.30 | +0.3<br>-0  | ±0.30 |
| 12-24p | ±0.40 | +0.4<br>-0  | ±0.40 |

| SIGN | DATE | DESCRIPTION                                           | APPROVER |
|------|------|-------------------------------------------------------|----------|
|      |      | <b>THIS IS CAD DRAWING, DO NOT REVISE MANUALLY!!!</b> |          |

Material:

- Item a :Male contact pin: Copper Tin plated
- Item b :Terminal(housing): Thermoplastic (UL94V-0)

Electrical: cULus

- Voltage rating: 300V
- Current rating: 8A
- Withstanding Voltage: 1.6 KV
- Operating temperature: -40°C to +115°C
- Soldering temperature: 250°C±10°C/5 Sec
- Safety Approval: cULus

NC xx 7 1 x 1 xxxx G

- |             |                     |                                                                        |
|-------------|---------------------|------------------------------------------------------------------------|
| 02 2 poles  | 0 Black (RAL9005)   | any special item by customer request, please contact sales department. |
| 03 3 poles  | 2 Red (RAL3001/D)   |                                                                        |
| ... ..      | 3 Orange(RAL2011/P) |                                                                        |
| 24 24 poles | 4 Yellow(RAL1018/A) |                                                                        |
|             | 5 Green(RAL6018/T)  |                                                                        |
|             | 6 Blue (RAL5015/A)  |                                                                        |
|             | 8 Grey(RAL7035/D)   |                                                                        |
|             | G: Pb<40,000ppm     |                                                                        |

**ANYTEK**

**CUSTOMER COPY**

ALL RIGHTS RESERVED. REPRODUCTION OR ISSUE TO THIRD PARTIES IN ANY FORM WHATEVER IS NOT PERMITTED WITHOUT WRITTEN AUTHORITY FROM THE PROPRIETOR. PROPERTY OF ANYTEK TECHNOLOGY CO., LTD

|          |               |                             |                      |          |            |
|----------|---------------|-----------------------------|----------------------|----------|------------|
| TITLE    |               | NC 5.0mm Right-angle Series |                      |          |            |
| PART NO. | NCxx71x1xxxxG |                             |                      | DWG NO.  | 8NC0002    |
| APPROVED | CHECKED       | DESIGNED                    | DRAWN                | CUST NO. |            |
|          |               | Runner<br>2010.08.16        | Runner<br>2010.08.16 |          | Tolerance  |
|          |               |                             |                      |          | X. ±0.50   |
|          |               |                             |                      |          | X.X ±0.30  |
|          |               |                             |                      |          | X.XX ±0.10 |
|          |               |                             |                      |          | X° ±1°     |