

For RoHS compliance
select plating code.




Fig. 1




Fig. 2




Fig. 3




Fig. 4

- Single row interconnects having an even number of pins are now available with a left or right hand footprint.
- Headers (850 & 852) use MM# 4006 pins. See page 175 for details.
- Sockets (851 & 853) use MM# 4890-0 receptacles and accept pin diameters from .015-.021. See page 131 for details.
- Coplanarity .005" (Single Row max 20 pins; Double Row max 40 pins). For higher pin counts contact technical support .
- Insulators are high temp. thermoplastic.



Ordering Information

Fig. 1L	Single Row Header, Left Hand Footprint Odd or Even # of pins			
	850-XX-0	-30-001000	Specify # of pins	02-50
Fig. 1R	Single Row Header, Right Hand Footprint Even # of pins			
	850-XX-0	-30-002000	Specify even # of pins	02-50
Fig. 2	Double Row Header, Even # of pins			
	852-XX-	-30-001000	Specify even # of pins	004-100
SPECIFY PLATING CODE XX=		10	90	40
Pin Plating		10μ" Au	200μ" Sn/Pb	200μ" Sn
Fig. 3L	Single Row Socket, Left Hand Footprint Odd or Even # of pins			
	★ 44 Plating Non-Standard	851-XX-0	-30-001000	Specify # of pins 02-50
Fig. 3R	Single Row Socket, Right Hand Footprint Even # of pins			
		851-XX-0	-30-002000	Specify even # of pins 02-50
Fig. 4	Double Row Socket, Even # of pins			
	★ 44 Plating Non-Standard	853-XX-	-30-001000	Specify even # of pins 004-100
SPECIFY PLATING CODE XX=		93	99	43 44
Sleeve (Pin)		200μ" Sn/Pb	200μ" Sn/Pb	200μ" Sn 200μ" Sn
Contact (Clip)		30μ" Au	200μ" Sn/Pb	30μ" Au 200μ" Sn