








- Material**
- Item ① Insulator body: Thermoplastic (UL 94V-0)
 - Item ② Insulating cover :Thermoplastic (UL94V-0)
 - Item ③ Contact pin : Brass ,Tin plated
 - Item ④ Wire guard: Stainless steel
 - Item ⑤ Pad board: Thermoplastic (UL94V-0)

- Electrical:**
- Voltage rating: 250V
 - Current rating: 8A
 - Wire range:
 - Solid wire(AWG): 12-28
 - Stranded wire(AWG): 12-28
 - Wire strip length: 8-9mm
 - Withstanding Voltage: 1.5KV
 - Operating temperature: -40°C to +115°C
 - Safety Approval: 
 - Critical dimension: 

- HM xx 90 x 1 xxxx G**
- ▲ RoHS compliant (lead<4%)
In copper Alloy
- No. OF POLES
- 01: 1 POLES
02: 2 POLES
16: 16 POLES
- ▲ COLOR
- 0 Black (RAL9005)
2 Red (RAL3001/D)
3 Orange(RAL2011/P)
4 Yellow(RAL1018/A)
5 Green(RAL6018/T)
6 Blue (RAL5015/A)
8 Grey(RAL7004/P)
9 White(RAL1102)
C Multiple colors
- 0000 Standard @ Logo
000A Standard ANY Logo
Any special item by customer request,
please contact sales department.



▲ N=NUMBER OF POLES

Dim L	(N-1)×7.5+6.50
Dim B	(N-1)×7.5

POLES	Dim L	Dim B
1p	±0.15	±0.15
2p-4p	±0.2	±0.15
5p-8p	±0.3	±0.25
9p-12p	±0.4	±0.35
13p-16p	±0.45	±0.4

SIGN	DATE	DESCRIPTION	APPROVER
▲	1/31/07	The soldering temperature from 245° to 250°	Aaron
▲	05/28'13	change the structure	Da cheng
▲	05/28'13	update the drawing	Da cheng
▲			
▲			

THIS IS CAD DRAWING, DO NOT REVISE MANUALLY!!!

ANYTEK

CUSTOMER COPY

ALL RIGHTS RESERVED. REPRODUCTION OR ISSUE TO THIRD PARTIES IN ANY FORM WHATSOEVER IS NOT PERMITTED WITHOUT WRITTEN AUTHORITY FROM THE PROPRIETOR. PROPERTY OF ANYTEK TECHNOLOGY CO., LTD

TITLE	HM7.5 mm Series Press fit Type			DWG NO.	8HM0004	Tolerance	
PART NO.	HMxx90xxxxG			CUST NO.		X.	±0.50
APPROVED	CHECKED	DESIGNED	DRAWN	UNIT:	mm	XX	±0.30
				SCALE:	NONE	XXX	±0.10
				SHEET:	01/01	REV:	F
						X*	±1°