

Printed: Sep 17, 2012


PRODUCT NUMBER	PIN OVERPLATING
10027011-1YYH	30u"/0.76u MIN (SEE NOTE 13) OVER 50u"/1.27u MIN Ni
↑ -2YYH	15u"/0.38u MIN (SEE NOTE 13) OVER 50u"/1.27u MIN Ni
-3YYH	50u"/1.27u MIN Au OVER 50u"/1.27u MIN Ni
-4YYH	100u"/2.54u MIN Sn OVER 50u"/1.27u MIN Ni (SEE NOTE 14)
-4YYHLF	
-5YYH	15u"/0.38u MIN (SEE NOTE 13) OVER 50u"/1.27u MIN Ni
-6YYH	30u"/0.76u MIN (SEE NOTE 13) OVER 50u"/1.27u MIN Ni
↓ -7YYH	30u"/0.76 MIN (SEE NOTE 15) OVER 50u"/1.27u MIN Ni
10027011-8YYH	15u"/0.38 MIN (SEE NOTE 15) OVER 50u"/1.27u MIN Ni

NOTES:


- BODY MATERIAL: 30% GLASS-FIBER REINFORCED PCT FLAME RETARDANT PER UL-94V-0. COLOR: BLACK.
OR
MINERAL FILLED LCP FLAME RETARDANT PER UL-94V-0. COLOR: BLACK.

PART NUMBERS WITH "H" SUFFIX TO 260°C PEAK TEMPERATURE FOR 20 SECONDS IN WAVE SOLDER, INFRA-RED OR VAPOR PHASE SOLDER PROCESS.

PART NUMBERS WITHOUT "H" SUFFIX TO 260°C PEAK TEMPERATURE FOR 20 SECONDS IN WAVE SOLDER, INFRA-RED OR VAPOR PHASE SOLDER PROCESS.
- PIN MATERIAL: PHOS-BRONZE.
- NUMBER OF POSITIONS FROM 2 TO 15.
- PART NUMBER WITHOUT SUFFIX ADDED PACKAGED IN POLYBAGS.
- MEASURED WITH PART IN RESTRAINED CONDITION.
- TWO SIDES OF PIN TIPS NOT PLATED TYPICAL BOTH ENDS.
- THIS SPECIAL PART CONFIGURATION REQUIRES CUSTOMER TO PROVIDE EXTERNAL HOLD-DOWN TO INSURE STABILITY DURING FIELD APPLICATION.
- 2 Lbs/0.9 Kg MIN PIN RETENTION IN EITHER DIRECTION.
- ADD "T" AS SUFFIX TO PART DASH NUMBER FOR TUBE PACKAGING.
EXAMPLE : 10027011--XYHT
- PART NUMBERS FOLLOWED BY A "W" SUFFIX ARE PACKAGED TAPE & REEL WITHOUT A PICK-UP CAP.
EXAMPLE : 10027011-XYHW



RECOMMENDED PAD LAYOUT
SCALE 5:1



DETAIL P
SCALE 10:1
TYP, BOTH ENDS

- ADD "LF" SUFFIX AT THE END OF PART NUMBER FOR LEAD FREE NOT AVAILABLE FOR -5YY, -5YYH, -6YY & -6YYH.
- THESE PRODUCTS MEETS EUROPEAN UNION DIRECTIVES AND OTHER COUNTRY REGULATION AS DESCRIBED IN GS-22-008.
- PLATING OPTIONS: MAY BE EITHER GOLD OR GXT PLATED AT MANUFACTURER'S CHOICE.
- "THIS PRODUCT HAS 100% TIN PLATING IN THE INTERFACE AND HAS NOT BEEN TESTED FOR WHISKER GROWTH IN ALL INTERCONNECT ENVIRONMENTS."
- PLATING OPTIONS: GOLD OR GXT ON CONTACT AREA AND 78~295u"/2~7.5u TIN ON SOLDER AREA.

mat'l. code				surface ISO 1302	tolerance ISO 406 ISO 1101	projection 	product family BERGSTIK			
ltr	ecn	no	dr	date	tolerances unless otherwise specified		title			
F					angles	linear	BERGSTIK® II HEADER SR. .100/2.54cc HORIZ. SMT.			
					0°±2°		dwg no			
					dr	L.POTTEIGER	4/7/03	sheet 2 of 2		
					enr	H. SUNDY	4/7/03	10027011		
					chr	H. SUNDY	4/7/03	A3		
					app	H. SUNDY	4/7/03	type Product Customer Drawing		
sheet index	revision	sheet								