

SIGN	DATE	DESCRIPTION	APPROVER
△	11/29'13	Add is cULus ///// update the drawing	Da cheng
△			
THIS IS CAD DRAWING, DO NOT REVISE MANUALLY!!!			

Material

- Item a Terminal Body: Thermoplastic (UL94V-0)
- Item b Female contact: Phbz, Tin plated
- Item c Wire guard: Stainless Steel
- Item d Insulating spacer :Thermoplastic (UL94V-0)
- Item e Terminal Cover: Thermoplastic (UL94V-0)

- △ Electrical cULus
- Voltage rating: 300V
 - Current rating: 10A
 - Wire range:
 - Solid wire(AWG): 14~26
 - Stranded wire(AWG): 14~26
 - Wire strip length: 10~11mm
 - Withstanding Voltage: 1.6KV
 - Operating temperature: -40°C to +115°C
 - △ Safety Approval: 
 - Critical dimension: 

HN xx 1 0 x 0 xxxx G

RoHS compliant
(lead<4%)
In copper Alloy

No. OF POLES
02 2 CONTACTS
03 3 CONTACTS
... ..
24 24 CONTACTS

△ Color

- 0 Black (RAL9005)
- 2 Red (RAL3001/D)
- 3 Orange(RAL2011/P)
- 4 Yellow(RAL1018/A)
- 5 Green(RAL6018/T)
- 6 Blue (RAL5015/A)
- 8 Grey(RAL7035/D)
- 9 White(RAL1102)
- C Green (RAL 6018/U)


0000: "@" Logo (Standard)
000A: "ANYTEK" Mark
Any special item by
customer request.
please contact sales
department.

ANYTEK

CUSTOMER COPY

ALL RIGHTS RESERVED. REPRODUCTION OR ISSUE TO THIRD PARTIES IN ANY FORM WHATEVER IS NOT PERMITTED WITHOUT WRITTEN AUTHORITY FROM THE PROPRIETOR. PROPERTY OF ANYTEK TECHNOLOGY CO., LTD

TITLE	HN 3.5 (2P~24P) series without fiange						
PART NO.	HNxx10x0xxxxG			DWG NO.	8HN0101		
APPROVED	CHECKED	DESIGNED	DRAWN	CUST NO.	Tolerance		
		Da cheng 2013.11.29	Da cheng 2013.11.29		UNIT: mm	X. ±0.50	
					SCALE: NONE	X.X ±0.30	
				SHEET: 01/01	REV.: C	X.XX ±0.10	
						X° ±1°	



DIMENSION

DIM L	Nx3.5
DIM P	(N-1)x3.5

N=Number of contacts

Poles	Tolerance	DIM L	DIM P
2pole~6pole		±0.15	±0.15
7pole~12pole		±0.20	±0.20
13pole~18pole		±0.25	±0.25
19pole~24pole		±0.30	±0.30