




SIZE	Part Num.	Threading	Headscrew	Packaging
25	8655MH2501BLF	UNC 4.40	Black	BULK (see note 1)
	8655MH2501BKLF	UNC 4.40	Black	KIT (see note 2)
	8655MH2502BLF	M3	Grey	BULK
	8655MH2502BKLF	M3	Grey	KIT



NOTES:

Material and finish: Zinc die-cast
Nickel plated

Cable strain relief: Polycarbonate (UL94V-0)

Jackscrews:

- Headscrew : plastic, color according threading
- Body : metal, threading according tables

Temperature range: -40°C to 120°C
Cable diameter: 4,0 to 13,0mm
Attenuation factor: >40 dB between 30MHz and 1 GHz
Marking FCI logo: Height 6 mm for all versions

Covers screwing force (max): 100 Ncm
Jackscrew screwing force (max): 50 Ncm


Packaging notes (see tables):

- 1 - Bulk : Every spare part packaged per 100 or 200 into plastic bag.5 plastic bags per carton box. 1 plastic bag per part.
- 2 - Kit : 1 set of spare parts necessary to realise 1 kit into a plastic bag. 100 plastic bags per carton box.

NOTE:RoHS INFORMATIONS

- The "LF" product meets European union Directives and other country regulations as described in GS-22-008.
- The product is not intended to be exposed to a manufacturing solder process.
- Packaging spec: see GS-14-920.

DESIGNATION	REP.	09	15	25	37
COVER BOTTOM	1		1		
JACKSCREW	2		2		
STRAIN RELIEF	3		2		
COVER TOP	4		1		
SCREW POZIDRIVE	5		2		

spec ref				dr	A Parrenin	2009/05/20	projection 	mm 	size	A3	scale	3:2
tolerance std ISO 406 ISO 1101	GENERAL TOLERANCES: ISO 2768-m			eng	D Detouillon	2017/01/16			ecn no	ELX-F-25931-1		
				chr	J Dalibard	2017/01/16						
				appr	Aymeric Soudy	2017/01/17						
surface  ISO 1302	linear	0.X	±/	Amphenol FCI	title D-SUB METAL HOODS STRAIGHT	dwg no	10085962			rev F		
		0.XX	±/									
		0.XXX	±/									
	angular	0°	±/°	www.fci.com	cat. no.	Product - Customer Drw			sheet 1 of 3			



A

B



C

D



SIZE	Part Num.	Threading	Headscrew	Packaging
09	8655MH0901BLF	UNC 4.40	Black	BULK (see note 1)
	8655MH0901BKLF	UNC 4.40	Black	KIT (see note 2)
	8655MH0902BLF	M3	Grey	BULK
	8655MH0902BKLF	M3	Grey	KIT



SIZE	Part Num.	Threading	Headscrew	Packaging
37	8655MH3701BLF	UNC 4.40	Black	BULK (see note 1)
	8655MH3701BKLF	UNC 4.40	Black	KIT (see note 2)
	8655MH3702BLF	M3	Grey	BULK
	8655MH3702BKLF	M3	Grey	KIT



SIZE	Part Num.	Threading	Headscrew	Packaging
15	8655MH1501BLF	UNC 4.40	Black	BULK (see note 1)
	8655MH1501BKLF	UNC 4.40	Black	KIT (see note 2)
	8655MH1502BLF	M3	Grey	BULK
	8655MH1502BKLF	M3	Grey	KIT



spec ref		dr		A Parrenin	2009/05/20	projection 	mm 	size	A3	scale	1:1		
tolerance std ISO 406 ISO 1101	GENERAL TOLERANCES: ISO 2768-m			eng	D Detouillon			2017/01/16	ecn no				ELX-F-25931-1
				chr	J Dalibard			2017/01/16	rel level				Released
				appr	Aymeric Soudy			2017/01/17	product family				
surface  ISO 1302	linear	0.X	± /	Amphenol FCi	title	D-SUB METAL HOODS STRAIGHT			dwg no	10085962		rev	F
		0.XX	± /										
		0.XXX	± /										
	angular	0°	± / °	www.fci.com	cat. no.	Product - Customer Drw				sheet 2 of 3			

A


B

C


D

CABLING INSTRUCTIONS FOR CABLE Ø 4, 5, 7 or 9 mm


1- Use two halves of strain relief, different sizes can be mixed (Ø4,5,7 or 9)



2- Strip cable 18mm and shape to two pigtails




3- Attach the strain relief around the cable




CABLING INSTRUCTIONS FOR CABLE Ø > 9 to 11 mm
1- Use one half of strain relief, (Ø9).


4- Bend cable shielding back on outside of strain relief




5- Mount connector and cable into the backshell



6- Assemble the other half screwing force: 100 Ncm



spec ref				dr	A Parrenin	2009/05/20	projection 	mm 	size	A3	scale	3:2
tolerance std ISO 406 ISO 1101	GENERAL TOLERANCES: ISO 2768-m			eng	D Detouillon	2017/01/16			ecn no ELX-F-25931-1			
				chr	J Dalibard	2017/01/16			rel level Released			
				appr	Aymeric Soudy	2017/01/17						
surface  ISO 1302	linear	0.X	±/	Amphenol FCi	title D-SUB METAL HOODS STRAIGHT				dwg no 10085962	rev F		
		0.XX	±/									
		0.XXX	±/									
		angular	0°	±/°	www.fci.com	cat. no.			Product - Customer Drw			sheet 3 of 3