






P.C.B Layout

|                  |
|------------------|
| DimL=N/2×3.5     |
| DimP=(N/2-1)×3.5 |
| DimK=(N/2-1)×3.5 |

N=Number of poles

| POLES       | Dim. Tol | Dim.L | Dim.P |
|-------------|----------|-------|-------|
| 2x2p-2x6p   |          | ±0.15 | ±0.10 |
| 2x7p-2x12p  |          | ±0.25 | ±0.20 |
| 2x13p-2x18p |          | ±0.35 | ±0.30 |
| 2x19p-2x24p |          | ±0.40 | ±0.35 |

| SIGN                                           | DATE     | DESCRIPTION         | APPROVER |
|------------------------------------------------|----------|---------------------|----------|
| △                                              | 04/25`11 | Material is changed | Chen Bo  |
| THIS IS CAD DRAWING, DO NOT REVISE MANUALLY!!! |          |                     |          |


Material:

- Item ③ Terminal housing: PA66 (UL94V-0)
- △ Item ⑤ Male contact pin: Brass, Tin plated

Electrical:

cULus

- Voltage rating: 150V
- Current rating: 7A
- Withstanding Voltage: 1.3KV
- Operating temperature: -40°C to +115°C
- Soldering temperature: 250°C±10°C/5 Sec
- Safety Approval: 



V X xx 1 0 x 0 xxxx G

No of plose  
04 2x2 CONTACTS  
06 3x2 CONTACTS  
...  
48 24x2 CONTACTS

0 Black  
3 Orange  
5 Green  
6 Blue  
8 Grey

RoHS  
Pb<40,000ppm  
0000 Standard @ Logo  
000A Standard ANY Logo  
Any special item by customer request, please contact sales department.

**ANYTEK**

**INSPECTION COPY**

ALL RIGHTS RESERVED. REPRODUCTION OR ISSUE TO THIRD PARTIES IN ANY FORM WHATEVER IS NOT PERMITTED WITHOUT WRITTEN AUTHORITY FROM THE PROPRIETOR. PROPERTY OF ANYTEK TECHNOLOGY CO., LTD

|          |         |                                    |                       |                                                                                       |             |           |            |
|----------|---------|------------------------------------|-----------------------|---------------------------------------------------------------------------------------|-------------|-----------|------------|
| TITLE    |         | VX 3.5mm Series Open type Vertical |                       |                                                                                       |             |           |            |
| PART NO. |         | VXxx10x0xxxxG                      |                       | DWG NO.                                                                               | 8VX0006     |           |            |
| APPROVED | CHECKED | DESIGNED                           | DRAWN                 | CUST NO.                                                                              | Tolerance   |           |            |
|          |         | Runner<br>2011.04.25               | Chen Bo<br>2011.04.25 |  | UNIT: mm    | X. ±0.50  |            |
|          |         |                                    |                       |                                                                                       | SCALE: NONE | X.X ±0.30 |            |
|          |         |                                    |                       | SHEET: 01/01                                                                          |             | REV: C    | X.XX ±0.10 |
|          |         |                                    |                       |                                                                                       |             |           | X° ±1°     |