




	Dim A	Dim B
2-6p	± 0.15	± 0.10
7-12p	± 0.20	± 0.15
13-18p	± 0.25	± 0.20
19-24p	± 0.30	± 0.25

$$\text{Dim } B = (N-1) \times 3.5$$

- Voltage rating: 300VAC/300VAC
- Current rating: 10A/10.5A
- Wire range: 1.5mm²
- ⚠ ● Solid wire(AWG): 16-28/16-28
- Stranded wire(AWG): 16-28/16-28
- Torque: 3Lb-In/0.2Nm
- Screw: M2
- Wire strip length: 6-7mm
- Withstanding Voltage: 1.6KV/2.5KV
- Operating temperature: -40°C to +115°C
- Safety Approval:

02	2 CONTACTS	0	Black (RAL9005)	0000	Standard @ Logo	Pb < 40,000ppm (RoHS)
03	3 CONTACTS	2	Red (RAL3001/D)	000A	Standard ANY Logo	
...	...	3	Orange(RAL2011/P)	0091	Standard ANY Logo	
24	24 CONTACTS	4	Yellow(RAL1018/A)	Any special item by customer request,		
		5	Green(RAL6018/T)	please contact sales		
		6	Blue (RAL5015/A)	department.		
		8	Grey(RAL7035/D)			





TJ3.81成品P數	TJ3.5拉柄P數
2P-4P	2P
5P-9P	5P
10P-15P	8P
16P-24P	12P

ANYTEK

CUSTOMER COPY

ALL RIGHTS RESERVED. REPRODUCTION OR ISSUE TO THIRD PARTIES IN ANY FORM WHATEVER IS NOT PERMITTED WITHOUT WRITTEN AUTHORITY FROM THE PROPRIETOR. PROPERTY OF ANYTEK TECHNOLOGY CO., LTD

TITLE	TJ-3.5mm Series with handle						
PART NO.	TJxx11x4xxxxG			DWG NO.	8TJ0547		
APPROVED	CHECKED	DESIGNED	DRAWN	CUST NO.			Tolerance
			Chen Bo 2010.07.09		UNIT: mm		X. ±0.50
					SCALE: NONE		X.X ±0.30
				SHEET: 01/01	REV: C		X.XX ±0.10
							X° ±1°



拉柄對應P數表

TJ3.81成品P數	TJ3.5拉柄P數
2P-4P	2P
5P-9P	5P
10P-15P	8P
16P-24P	12P

N = Number of poles
Dim A=Nx3.81
Dim B=(N-1)x3.81

	Dim A	Dim B
2-6p	±0.15	±0.10
7-12p	±0.20	±0.15
13-18p	±0.25	±0.20
19-24p	±0.30	±0.25

SIGN	DATE	DESCRIPTION	APPROVER
△	12/04'08	The wire entry hole was changed.	Jacke
△	12/04'08	Electrical standard changed.	Jacke
△	12/04'08	Add the tolerance table	Jacke
△	2010.07.12	The solid and Stranded wire is changed from16-26 to16-28	Chen Bo
△	2010.07.12	Rrmove the CSA mark	Chen Bo
THIS IS CAD DRAWING, DO NOT REVISE MANUALL Y!!!			

Material

- Item① Clamp: Brass(CuZn) Ni plated
- Item② Terminal screw: Steel Zinc plating "-" slot type
- Item③ Female contact: PhBz ,Tin plated
- Item④ Terminal (Cover): Thermoplastic (UL94V-0)
- Item⑤ Terminal (Body): Thermoplastic (UL94V-0)
- Item⑥ Handle: Thermoplastic (UL94V-0)

△ Electrical cULus/VDE

- Voltage rating: 300VAC/300VAC
- Current rating: 10A/10.5A
- Wire range: 1.5mm²
- Solid wire(AWG): 16-28/16-28
- Stranded wire(AWG): 16-28/16-28
- Torque: 3Lb-In/0.2Nm
- Screw: M2
- Wire strip length: 6-7mm
- Withstanding Voltage: 1.6KV/2.5KV
- Operating temperature: -40°C to +115°C
- Safety Approval: cULus VDE

TJ xx 31 x 4 xxxx G

02 2 CONTACTS
03 3 CONTACTS
...
24 24 CONTACTS

0 Black (RAL9005)
2 Red (RAL3001/D)
3 Orange(RAL2011/P)
4 Yellow(RAL1018/A)
5 Green(RAL6018/T)
6 Blue (RAL5015/A)
8 Grey(RAL7035/D)

Pb < 40,000ppm (RoHS)
000 0 Standard @ Logo
000 A Standard ANY Logo
Any special item by customer request, please contact sales department.

ANYTEK

CUSTOMER COPY

ALL RIGHTS RESERVED. REPRODUCTION OR ISSUE TO THIRD PARTIES IN ANY FORM WHATSOEVER IS NOT PERMITTED WITHOUT WRITTEN AUTHORITY FROM THE PROPRIETOR. PROPERTY OF ANYTEK TECHNOLOGY CO., LTD

TITLE		TJ-3.81mm Series With handle						
PART NO.		TJxx31x4xxxxG			DWG NO.	8TJ0653		
APPROVED	CHECKED	DESIGNED	DRAWN	CUST NO.			Tolerance	
			Chen Bo 2010.07.12		UNIT: mm		X.	±0.50
					SCALE: NONE		X.X	±0.30
					REV.: D		X.XX	±0.10
SHEET: 01/01						X°	±1°	