





1

2

3



PART NO. AND CH. CODE	MATERIAL	COLOR
7182-8559-30	PBT	BLACK
7182-8558-10	PBT	DARK GRAY

GENERAL TOLERANCE											
	10 MAX	50 MAX	100 MAX	250 MAX	250 OVR	R5 MAX	R10 MAX	R20 MAX	R20 OVR	ANGLE	ECCENT
A	±0.15	±0.2	±0.3	±0.5	±0.75					±3°	0.1
B	±0.2	±0.3	±0.55	±0.95	±1.4	±0.2	±0.3	±0.5	±2.5	±3°	0.1
(C)	±0.3	±0.5	±0.8	±1.4	±2					±3°	0.15

注 記

1. 適用端子品番 : 7114-4102-02 (CAVS 0.3~0.5)

7114-4103-02 (CAVS 0.85~1.25)

7114-4102-08 (CAVS 0.3~0.5)

7114-4103-08 (CAVS 0.85~1.25)

2. 適用ゴム栓品番 : 7158-3030-50 (CAVS 0.3~0.5)

7158-3031-90 (CAVS 0.85~1.25)

NOTES

1. APPLICABLE TERMINAL NO. : 7114-4102-02 (CAVS 0.3~0.5)

7114-4103-02 (CAVS 0.85~1.25)

7114-4102-08 (CAVS 0.3~0.5)

7114-4103-08 (CAVS 0.85~1.25)

2. APPLICABLE RUBBER STOPPER NO. : 7158-3030-50 (CAVS 0.3~0.5)

7158-3031-90 (CAVS 0.85~1.25)

ISSUE MARK

								CUSTOMER				MATL. SPEC.				SEE TABLE		TREAT. & FIN.																			
								CUSTOMER PART NO.				CUSTOMER DWG NO.																									
⚠	10/10/15	CHANGED PART NAME			C10-ZA77	J. G									NAME ⚠ 060 4P SEALED HOUSING MALE (TYPE-B)																						
	02/10/02	NEW			CO2-X883	K. Y	OFFICE				TRIAL PART NO.																										
LET	DATE	REVISION RECORD			NO.	CHKD	VENDOR																														
GENERAL TOLERANCE							VENDOR NO.																														
	10MAX	50MAX	100MAX	250MAX	2500VR	ANGLE	ECCENT	DWG TYPE		DWG SOURCE		DWG DATE		UNIT	SCL	ANGLE	PART NO.																				
A	±0.15	±0.2	±0.3	±0.5	±0.75	±30'	0.1	R		NEW		02/10/02		mm	2:1	3	7182-8559-30 ETC.																				
B	±0.2	±0.3	±0.55	±0.95	±1.4	±30'	0.1	APPROVED		CHECKED		CHECKED		DESIGN		DRAWN		CH. CODE																			
C	±0.3	±0.5	±0.8	±1.4	±2	±30'	0.15											DWG NO.																			
SPECIFIED							MASS							S. MIZUSE				R. DE GUZMAN				K. YOSHIDA				J. GAMBOA				7182-8559-30:R		SET DRW NO.					
														10/10/15								10/10/15				02/03/11				10/10/15				YAZAKI CORPORATION			