


PART NO. AND CH. CODE	ΔL_4	H ₁	H ₂	W ₁	R ₁	W ₂	R ₂	WIRE SIZE (mm ²)
7114-4110-02, Δ	13.00	Δ (2.45)	Δ (3.55)	2.30	0.45	2.80	0.45	Δ 0.3~0.6 OR EQUIVALENT
7114-4111-02, Δ	13.00	Δ (3.25)	Δ (4.45)	3.00	0.65	3.60	0.65	Δ 0.75~1.25 OR EQUIVALENT
7114-4112-02, Δ	13.00	Δ (4.00)	Δ (5.50)	3.70	0.85	4.60	0.90	1.5~2.5 OR EQUIVALENT
Δ 7114-4113-02, Δ	18.50	(5.40)	(7.05)	4.90	1.50	6.50	1.50	3.0~5.0 OR EQUIVALENT

注 記

- 適合相手品番: 7116-4110-02 ETC.
 - 7114-4113-02 における通電流値は、2.5 mm²電線相当以下とする。
 - 7114-4113-02 に 5 mm²電線を圧着して使用する場合には、専用ハウジングが必要です。
- NOTES
- MATING PART NO.: 7116-4110-02 ETC.
 - CURRENT FOR 7114-4113-02 SHALL BE THE CURRENT FOR 2.5 mm² WIRE OR UNDER.
 - IN CASE 5 mm² WIRE IS CRIMPED WITH THE TERMINAL 7114-4113-02,
SPECIAL HOUSING IS REQUIRED.

B

B



A

A

Δ	03.07.07	CHANGED WIRE SIZE & CORRECTION OF A CLERICAL ERROR	C03-X433	K.0
Δ	99.10.11	ADDED NOTE ETC.	C99-7133	T.S
Δ	99.02.17	ADDED PART NO. ETC.	C99-1408	Y.U
Δ	97.07.25	CHANGED FORM, Δ	C97-M151	H.K
—	95.07.25	NEW	C95-M193	Y.U
LET	DATE	REVISION RECORD	NO.	CHKD
GENERAL TOLERANCE				
10MAX	50MAX	100MAX	250MAX	2500VR
A ± 0.15	± 0.2	± 0.3	± 0.5	± 0.75
B ± 0.2	± 0.3	± 0.55	± 0.95	± 1.4
C ± 0.3	± 0.5	± 0.8	± 1.4	± 2
SPECIFIED				MASS
				g

MATL. COPPER ALLOY t=0.3 TREAT.
SPEC. (TIN PLATING) & FIN.NAME Δ 2.8 SYSTEM CONNECTOR
MALE TERMINALPART NO.
CH. CODE

7114-4110-02 ETC.

DWG NO.

SET DWG NO.

7114-4110-02:R

Y. UCHIDA Y. OHKUBO

YAZAKI CORPORATION