

## Data sheet

## 3RA2135-4PD35-0AK6

Combination Starter Non Reversing Fast Bus FLA Range 28-36A 3 Pole 120VAC Coil S2 Open Type 1NO <(>&<)> 1NC Aux	
product brand name	SIRIUS
product designation	non-fused motor starter 3RA2
design of the product	direct starter
manufacturer's article number	
• of the supplied contactor	<a href="#">3RT2035-1AK60</a>
• of the supplied circuit-breakers	<a href="#">3RV2031-4PA15</a>
• of the supplied busbar adapter	<a href="#">8US1261-6MT10</a>
• of the supplied link module	<a href="#">3RA2931-1AA00</a>
<b>General technical data</b>	
size of the circuit-breaker	S2
size of load feeder	S2
product extension auxiliary switch	Yes
insulation voltage with degree of pollution 3 at AC rated value	690 V
degree of pollution	3
surge voltage resistance rated value	6 kV
shock resistance according to IEC 60068-2-27	6g / 11 ms
mechanical service life (operating cycles) of contactor typical	10 000 000
type of assignment	2
Weight	2.76 kg
<b>Ambient conditions</b>	
ambient temperature	<ul style="list-style-type: none"> <li>• during operation -20 ... +60 °C</li> <li>• during storage -50 ... +80 °C</li> <li>• during transport -55 ... +80 °C</li> </ul>
<b>Main circuit</b>	
number of poles for main current circuit	3
design of the switching contact	electromechanical
adjustable current response value current of the current-dependent overload release	28 ... 36 A
operating voltage	<ul style="list-style-type: none"> <li>• rated value 690 V</li> <li>• at AC-3 rated value maximum 690 V</li> </ul>
operating frequency rated value	50 ... 60 Hz
operational current at AC-3 at 400 V rated value	35 A
operating power at AC-3	
• at 400 V rated value 18 500 W	
<b>Control circuit/ Control</b>	
control supply voltage at AC	
• at 50 Hz rated value 110 V	
• at 50 Hz rated value 88 ... 121 V	
• at 60 Hz rated value 120 V	
• at 60 Hz rated value 96 ... 132 V	
apparent holding power of magnet coil at AC	16 VA
inductive power factor with the holding power of the coil	0.37
<b>Auxiliary circuit</b>	
number of NC contacts for auxiliary contacts	2
number of NO contacts for auxiliary contacts	2
<b>Protective and monitoring functions</b>	
trip class	CLASS 10
design of the overload release	thermal (bimetallic)
response value current of instantaneous short-circuit trip unit	468 A

UL/CSA ratings	
<b>yielded mechanical performance [hp]</b>	
• for single-phase AC motor	
— at 110/120 V rated value	3 hp
• for 3-phase AC motor	
— at 200/208 V rated value	10 hp
Short-circuit protection	
<b>product function short circuit protection</b>	Yes
<b>design of the short-circuit trip</b>	magnetic
<b>conditional short-circuit current (Iq)</b>	
• at 400 V according to IEC 60947-4-1 rated value	100 000 A
Installation/ mounting/ dimensions	
<b>mounting position</b>	vertical
<b>fastening method</b>	for snapping onto 60 mm busbar systems
<b>height</b>	350 mm
<b>width</b>	55 mm
<b>depth</b>	208 mm
<b>required spacing</b>	
• for grounded parts	
— forwards	0 mm
— backwards	6 mm
— upwards	50 mm
— at the side	10 mm
— downwards	10 mm
• for live parts	
— forwards	0 mm
— backwards	6 mm
— upwards	50 mm
— downwards	10 mm
— at the side	10 mm
Connections/ Terminals	
<b>type of electrical connection for main current circuit</b>	screw-type terminals
<b>type of connectable conductor cross-sections for main contacts</b>	1 ... 35 mm <sup>2</sup> , 2x (1 ... 16 mm <sup>2</sup> )
<b>connectable conductor cross-section for main contacts finely stranded with core end processing</b>	1 ... 25 mm <sup>2</sup>
Safety related data	
<b>proportion of dangerous failures with high demand rate according to SN 31920</b>	73 %
<b>B10 value with high demand rate according to SN 31920</b>	1 000 000
<b>Electrical Safety</b>	
<b>protection class IP on the front according to IEC 60529</b>	IP20
<b>touch protection on the front according to IEC 60529</b>	finger-safe, for vertical contact from the front
Approvals Certificates	
<b>General Product Approval</b>	<b>For use in hazardous locations</b>

[Confirmation](#)



[Test Certificates](#)

[Marine / Shipping](#)

[Special Test Certificate](#)



[Marine / Shipping](#)

[other](#)

[Railway](#)

[Dangerous goods](#)

[Environment](#)

[Confirmation](#)[Special Test Certificate](#)[Transport Information](#)[Environmental Confirmations](#)

#### Further information

Information on the packaging

<https://support.industry.siemens.com/cs/ww/en/view/109813875>

Information- and Downloadcenter (Catalogs, Brochures,...)

<https://www.siemens.com/ic10>

Industry Mall (Online ordering system)

<https://mall.industry.siemens.com/mall/en/en/Catalog/product?mlfb=3RA2135-4PD35-0AK6>

Cax online generator

<http://support.automation.siemens.com/WW/CAxorder/default.aspx?lang=en&mlfb=3RA2135-4PD35-0AK6>

Service&Support (Manuals, Certificates, Characteristics, FAQs,...)

<https://support.industry.siemens.com/cs/ww/en/ps/3RA2135-4PD35-0AK6>

Image database (product images, 2D dimension drawings, 3D models, device circuit diagrams, EPLAN macros, ...)

[http://www.automation.siemens.com/bilddb/cax\\_de.aspx?mlfb=3RA2135-4PD35-0AK6&lang=en](http://www.automation.siemens.com/bilddb/cax_de.aspx?mlfb=3RA2135-4PD35-0AK6&lang=en)

Characteristic: Tripping characteristics, I<sup>t</sup>, Let-through current

<https://support.industry.siemens.com/cs/ww/en/ps/3RA2135-4PD35-0AK6/char>

Further characteristics (e.g. electrical endurance, switching frequency)

<http://www.automation.siemens.com/bilddb/index.aspx?view=Search&mlfb=3RA2135-4PD35-0AK6&objecttype=14&gridview=view1>

---

last modified:

12/15/2020