




SIGN	DATE	DESCRIPTION	APPROVER
△	2010.12.08	Added "cULus" standard	Chen Bo
△	2012.02.23	Flange nut is changed	Aaron
△	2012.02.23	The dimension is added	Aaron
△	2012.02.23	The material is changed from Brass to Copper	Aaron
△	2014.06.05	change the dimension from A1.70 to 1.00	Ji long
△	2014.11.13	update drawing	Evan
THIS IS CAD DRAWING, DO NOT REVISE MANUALLY!!!			

Material

- Item ① Long contact pin: Copper ,Tin plated
- Item ② Short contact pin: Copper ,Tin plated
- Item ③ Terminal (housing): Thermoplastic (UL94V-0)
- Item ④ With flange nut: Brass ,M2.5

Electrical

- Voltage rating: 300VAC
- Current rating: 10A
- Withstanding Voltage: 1.6KV
- Operating temperature: -40°C to +115°C
- Soldering temperature: 260°C±5°C/5 Sec
- Safety Approval:
- Critical dimension:

No. OF POLES **VF xx 3 2 x 0 xxxx G**

No. OF POLES
04: 2x2 POLES
...
24: 2x12 POLES

Color
0 Black (RAL9005)
2 Red (RAL3001/D)
3 Orange(RAL2011/P)
4 Yellow(RAL1018/A)
5 Green(RAL6018/T)
6 Blue (RAL5015/A)
8 Grey(RAL7035/D)
9 White(RAL1102)
C Green(RAL6018/U)

RoHS compliant (lead<4%)
In copper Alloy

0000: "@" Logo (Standard)
000A: "ANYTEK" Mark
Any special item by customer request, please contact sales department.

Fill the glue

△	Dim.L	$(N/2) \times 3.81 + 0.79$
	Dim.B	$(N/2 - 1) \times 3.81$
△	Dim.C	$(N/2 - 1) \times 3.81$
△	Dim.D	$(N/2 - 1) \times 3.81$
△	Dim.E	$((N/2) + 1) \times 3.81 + 1.38$
△	Dim.F	$(N/2 + 2) \times 3.81 + 2.77$

N= number of poles △	
Poles	Tolerance
2x2P-2x5P	±0.15
2x6P-2x10P	±0.20
2x11P-2x12P	±0.25

ANYTEK

CUSTOMER COPY
ALL RIGHTS RESERVED. REPRODUCTION OR ISSUE TO THIRD PARTIES IN ANY FORM WHATEVER IS NOT PERMITTED WITHOUT WRITTEN AUTHORITY FROM THE PROPRIETOR. PROPERTY OF ANYTEK TECHNOLOGY CO., LTD

TITLE VF-3.81 Series 2x2P-2x16P Vertical With flange		DWG NO. 8VF0204	
PART NO.	VFxx32x0xxxxG	CUST NO.	
APPROVED	CHECKED	DESIGNED	DRAWN
		Evan 11/13`14	Evan 11/13`14
		UNIT: mm	X. ±0.50
		SCALE: NONE	X.X ±0.30
SHEET: 01/01		REV.: F	X.XX ±0.10
			X° ±1°