









NOTES:

1. METALSHELLS: STEEL; min. 315µin TIN over 40-80µin NICKEL
2. INSULATORS: PBT GF UL 94 V-0, GREEN
3. SIGNAL CONTACTS: COPPER ALLOY
PLATING: GOLD FLASH over NICKEL
4. HIGH POWER CONTACTS 20A: COPPER ALLOY
PLATING MATING AREA: GOLD FLASH over NICKEL
PLATING TERMINATION SIDE: 160-240µin TIN over 80µin NICKEL
5. CONNECTOR IS PART MARKED: 3017W2SAR69A10X CONEC ABC

Directive 2002/95/EC RoHS compliant

THIS DRAWING MAY NOT BE COPIED OR REPRODUCED IN ANY WAY, AND MAY NOT BE PASSED ON TO A THIRD PARTY WITHOUT WRITTEN PERMISSION. OWNERSHIP AND COPYRIGHT OF CONEC GmbH				tolerance			scale: 2:1 (5:1)			
							dim. in mm		material: SEE NOTES	
								date	name	title: D-SUB COMBINATION FEMALE 17W2S with threaded rear spacer
								drawn	21.06.12 Henneboel	
								appd.	21.06.12 Koch	
				norm						
				d-old						
						dwg no: 13K1A3990	DIN-A3 sh: 1			
a	Original									
rev.	description	date	name			part no: 3017W2SAR69A10X				