



SIGN	DATE	DESCRIPTION	APPROVER
△	02/08'07	Part No. is changed.	Aaron
△	07/14'11	Electrical is changed	Runner
THIS IS CAD DRAWING, DO NOT REVISE MANUALLY!!!			

### Material

- Item 1 Insulating body Thermoplastic ( UL94V-0 )
- Item 2 Insulating lever Thermoplastic ( UL94V-0 )
- Item 3 Female contact: PhBz ( CuSn ) Tin plated

### △ Electrical

- Voltage rating:300V
- Current rating:5A
- Wire range:
- Solid wire(AWG):20-22
- Stranded wire(AWG):20-22
- Wire strip length:
- Withstanding Voltage:1.6KV
- Operating temperature:-40℃ to +115℃
- Safety Approval: us
- Critical dimension: 

### PART NO.

HP xx 30 x 0 xxxx G △

Poles	Color	0000 Standard @ Logo
02 2Contacts	0 Black	000A Standard ANY Logo
03 3Contacts	5 Green ( RAL 6018/T )	Any special item by
..	6 Blue	customer request,
24 24Contacts	8 Grey ( RAL 7004/P )	please contact sales
		department.

RoHS  
Pb<40,000ppm

SECTION P-P


N = Number of poles  
Dim A=(N-1)x3.81+4.6  
Dim B=(N-1)x3.81

	Dim A	Dim B
2-6p	±0.15	±0.15
7-12p	±0.20	±0.20
13-18p	±0.25	±0.25
19-24p	±0.30	±0.30

# ANYTEK

## CUSTOMER COPY

ALL RIGHTS RESERVED. REPRODUCTION OR ISSUE TO THIRD PARTIES IN ANY FORM WHATEVER IS NOT PERMITTED WITHOUT WRITTEN AUTHORITY FROM THE PROPRIETOR. PROPERTY OF ANYTEK TECHNOLOGY CO., LTD

TITLE		HP 3.81 Series without flange			DWG NO.		8HP0201	
PART NO.		HPxx30x0xxxxG			CUST NO.			
APPROVED		CHECKED	DESIGNED	DRAWN	Tolerance			
			Runner	Aaron				
			2011.07.14	2007.02.08				
					UNIT: mm		X. ±0.50	
					SCALE: NONE		X.X ±0.30	
							X.XX ±0.10	
							X° ±1°	
					SHEET: 01/01		REV.: E	