

[illegible][illegible][illegible]

RoHs

Technical Index:

- The surface of the plastic parts should be smooth,no rough edges,no obvious shrinkage,defects,cracks and other phenomena)
- Lock Configuration: 2 to 3Pin is 1, ≥ 4Pin is 2
- Temperature range: -25° C~+85° C.
- Rated voltage: 125V, AC/DC.
- Contact resistance: ≤0.02 Ω.
- Insulation resistance:≥100M Ω

Part No **Pin** **A** **B** **C**

W1251110-2PR2123	2	1.25	3.20	4.30
W1251110-3PR2123	3	2.50	4.45	5.55
W1251110-4PR2123	4	3.75	5.70	6.80
W1251110-5PR2123	5	5.00	6.95	8.05
W1251110-6PR2123	6	6.25	8.20	9.30
W1251110-7PR2123	7	7.50	9.45	10.55
W1251110-8PR2123	8	8.75	10.70	11.80
W1251110-9PR2123	9	10.00	11.95	13.05
W1251110-10PR2123	10	11.25	13.20	14.30
W1251110-11PR2123	11	12.50	14.45	15.55
W1251110-12PR2123	12	13.75	15.70	16.80
W1251110-13PR2123	13	15.00	16.95	18.05
W1251110-14PR2123	14	16.25	18.20	19.30
W1251110-15PR2123	15	17.50	19.45	20.55
W1251110-16PR2123	16	18.75	20.70	21.80
W1251110-17PR2123	17	20.00	21.95	23.05
W1251110-18PR2123	18	21.25	23.20	24.30
W1251110-19PR2123	19	22.50	24.45	25.55
W1251110-20PR2123	20	23.75	25.70	26.80

DIMA ±0.1
1.25
Ø0.60
胶芯外形
适用线路板 (PCB LAYOUT)

GENERAL TOLERANCES UNLESS SPECIFIED

X.° ±0.50	X.° ±5°
X.X° ±0.20	X.X° ±3°
X.XX° ±0.10	X.XX° ±1°

PART NO.
W1251110-XPR2123

TITLE:
1.25 PITCH H4.7 S/T WIRE TO BOARD DIP CONN.

DESIGN: James

CUSTOMER:

CHED: Talen

SCALE:

APPD: Sophia

SHEET: 1/1

MANUFACTURE DWG

LOCK CONFIGURATION(锁扣位置)

SECTION A-A

适

1 2 3 4 5 6 7 8

RoHs

1.25 ± 0.1 (PITCH)
DIMA ± 0.2
DIMB ± 0.15
DIMC ± 0.2

A

0.62
N-0.30 ± 0.02

Technical Index:

- The surface of the plastic parts should be smooth, no rough edges, no obvious shrinkage, defects, cracks and other phenomena)
- Lock Configuration: 2 to 3Pin is 1, ≥ 4Pin is 2
- Temperature range: -25° C ~ +85° C.
- Rated voltage: 125V, AC/DC.
- Contact resistance: ≤ 0.02 Ω.
- Insulation resistance: ≥ 100M Ω

7.00 ± 0.2
4.70 ± 0.15
0.40 ± 0.05
1.30 ± 0.2
3.20

3.00
2.45

SECTION A-A

Part No Pin A B C

W1251110-2PR2123	2	1.25	3.20	4.30
W1251110-3PR2123	3	2.50	4.45	5.55
W1251110-4PR2123	4	3.75	5.70	6.80
W1251110-5PR2123	5	5.00	6.95	8.05
W1251110-6PR2123	6	6.25	8.20	9.30
W1251110-7PR2123	7	7.50	9.45	10.55
W1251110-8PR2123	8	8.75	10.70	11.80
W1251110-9PR2123	9	10.00	11.95	13.05
W1251110-10PR2123	10	11.25	13.20	14.30
W1251110-11PR2123	11	12.50	14.45	15.55
W1251110-12PR2123	12	13.75	15.70	16.80
W1251110-13PR2123	13	15.00	16.95	18.05
W1251110-14PR2123	14	16.25	18.20	19.30
W1251110-15PR2123	15	17.50	19.45	20.55
W1251110-16PR2123	16	18.75	20.70	21.80
W1251110-17PR2123	17	20.00	21.95	23.05
W1251110-18PR2123	18	21.25	23.20	24.30
W1251110-19PR2123	19	22.50	24.45	25.55
W1251110-20PR2123	20	23.75	25.70	26.80


DIMA ± 0.1
1.25
Ø 0.60
胶芯外形
适用线路板 (PCB LAYOUT)

序号	品名	材质
1	1.25 Pitch S/T Wire To Board Housing DIP (H=4.7)	PA66 UL94V-2 Red
2	1.25 Pitch S/T Wire To Board Terminal DIP (H=4.7)	Copper Alloy/ Tin Plating

LOCK CONFIGURATION (锁扣位置)

GENERAL TOLERANCES UNLESS SPECIFIED		PART NO.		TITLE:	
X.° ±0.50	X.° ±5°	W1251110-XPR2123	DESIGN: James	1.25 PITCH H4.7 S/T WIRE TO BOARD DIP CONN.	
X.X° ±0.20	X.X° ±3°			CUSTOMER	
X.XX° ±0.10	X.XX° ±1°	CHED: Talen	APPD: Sophia	SIZE A4	UNITS MM
MANUFACTURE DWG		SCALE N:A		SHEET 1/1	

深圳市华明通电子有限公司
Shenzhen Huamingtong Electronics Co., Ltd



1 2 3 4 5 6 7 8

RoHs

1.25 ± 0.1 (PITCH)
DIMA ± 0.2
DIMB ± 0.15
DIMC ± 0.2

A

0.62
N-0.30 ± 0.02

Technical Index:

- The surface of the plastic parts should be smooth, no rough edges, no obvious shrinkage, defects, cracks and other phenomena)
- Lock Configuration: 2 to 3Pin is 1, ≥ 4Pin is 2
- Temperature range: -25° C ~ +85° C.
- Rated voltage: 125V, AC/DC.
- Contact resistance: ≤ 0.02 Ω.
- Insulation resistance: ≥ 100M Ω

7.00 ± 0.2
4.70 ± 0.15
0.40 ± 0.05
1.30 ± 0.2
3.20

3.00
2.45

SECTION A-A

Part No Pin A B C

W1251110-2PR2123	2	1.25	3.20	4.30
W1251110-3PR2123	3	2.50	4.45	5.55
W1251110-4PR2123	4	3.75	5.70	6.80
W1251110-5PR2123	5	5.00	6.95	8.05
W1251110-6PR2123	6	6.25	8.20	9.30
W1251110-7PR2123	7	7.50	9.45	10.55
W1251110-8PR2123	8	8.75	10.70	11.80
W1251110-9PR2123	9	10.00	11.95	13.05
W1251110-10PR2123	10	11.25	13.20	14.30
W1251110-11PR2123	11	12.50	14.45	15.55
W1251110-12PR2123	12	13.75	15.70	16.80
W1251110-13PR2123	13	15.00	16.95	18.05
W1251110-14PR2123	14	16.25	18.20	19.30
W1251110-15PR2123	15	17.50	19.45	20.55
W1251110-16PR2123	16	18.75	20.70	21.80
W1251110-17PR2123	17	20.00	21.95	23.05
W1251110-18PR2123	18	21.25	23.20	24.30
W1251110-19PR2123	19	22.50	24.45	25.55
W1251110-20PR2123	20	23.75	25.70	26.80

DIMA ± 0.1
1.25
Ø 0.60
胶芯外形

适用线路板 (PCB LAYOUT)

序号	品名	材质
1	1.25 Pitch S/T Wire To Board Housing DIP (H=4.7)	PA66 UL94V-2 Red
2	1.25 Pitch S/T Wire To Board Terminal DIP (H=4.7)	Copper Alloy/ Tin Plating

LOCK CONFIGURATION (锁扣位置)

GENERAL TOLERANCES UNLESS SPECIFIED		PART NO.		TITLE:	
X.° ±0.50	X.° ±5°	W1251110-XPR2123	JAMES	1.25 PITCH H4.7 S/T WIRE TO BOARD DIP CONN.	
X.X° ±0.20	X.X° ±3°			CUSTOMER	
X.XX° ±0.10	X.XX° ±1°	CHD: Talen	APPD: Sophia	SIZE A4	UNITS MM
MANUFACTURE DWG		SCALE N:A		SHEET 1/1	