

03

Technical drawing of a roller guide assembly. The drawing shows a side view of the assembly with various dimensions and callouts. The main body is a rectangular block with a threaded section on the left. The top section is a cylindrical roller guide assembly. The dimensions are as follows:

- Top width: .470
- Roller diameter: $\varnothing .750$
- Roller width: $\varnothing .5 \times .12$ WIDE CORROSION RESISTANT STEEL ROLLER
- Roller guide lock ring: $\triangle 7$
- Hex nut: 2X HEX NUT .812 ACROSS FLATS X .125 THICK $\triangle 7$
- Internal tooth lockwasher: CORROSION RESISTANT STEEL INTERNAL TOOTH LOCKWASHER, $\varnothing .87 \times (.022)$ THICK $\triangle 7$
- Keying washer: CORROSION RESISTANT STEEL KEYING WASHER $\varnothing .87 \times .040$ THICK, TAB .110 WIDE $\triangle 7$
- Thread: 5/8-24 UNEF THREAD TO WITHIN .125 OF SHOULDER
- Bottom width: $1.0 \pm .4$
- Bottom height: .050

PLATOR

TCH
U.S.A.

ANSI Y14.5M-1982 APPLIES

WEIGHT 12 OZ MAX

[illegible]