

8LT, 8ST & 8D Series Reinforced Sealing



38999 Connector with Reinforced Sealing

Resin sealed for harsh environment applications. Up to 1000 times higher sealing than standard version.

Wide availability ■ All 38999 layouts.
Aluminum, including RoHS Black Zinc Nickel.
Composite for ultra low weight.
Titanium or stainless steel for outdoor application.

Fully intermateable ■ 8LT with MS27466 or HE308.
8ST with VG96912 or JN1003.
8D with D38999, EN3645 or BACC63CT/DB.

Temperature ■ Fast temperature change: from -55°C to 125°C.
Compatible with wave or iron soldering.

Contacts ■ PC tail or solder contacts.
Male or female contacts.
Tin plated version available.
Shoulderless contact available, consult us.



Description

- Reinforced sealed receptacle with male or female straight PC tail contacts
- Strong sealing performance: 10^{-7} atm.cm³/s
- Designed for unpressurized area
- 125°C max (operational temperature)
- 100 % scoop proof
- Full RoHS solution
- High density connectors
- Weight saving compared to hermetic version
- Other SOURIAU ranges on request

Technical features

Mechanical

- **Shell plating:**
 - . 8LT & 8ST aluminum shell:
 - . Black zinc nickel (Z)
 - . Olive drab cadmium (B)
 - . Nickel (F)
 - . 8D aluminum shell:
 - . Black zinc nickel (Z)
 - . Olive drab cadmium (W)
 - . Nickel (F)
 - . 8D composite shell:
 - . Olive drab cadmium (J)
 - . Nickel (M)
 - . 8D stainless steel shell:
 - . Nickel (S)
 - . Passivated (K)
 - . 8D titanium shell:
 - . Nickel (TF)
 - . Without plating (TT)
- **Insulator:** Thermoplastic
- **Interfacial seal:** Silicone elastomer
- **Contacts:** Copper alloy
- **Contacts plating:** Gold over nickel plated
- **Endurance:**
 - 500 mating/unmating operations

Electrical

- **Contact resistance:**

Contacts size	26	22	20	16	12	8	4
Resistance mΩ	16	14.6	7.3	3.8	3.5	3	2


- **Shielding:**
 - . 8LT: . 90db - 100MHz
 - . . 50db - 10GHz
 - . 8ST: . 70 db - 100MHz
 - . 8D: . F; S; TF: 65db - 10GHz
 - . . F; Z; W; J; M: 85db - 1GHz
 - . . Z; W: 50db - 10GHz
 - . . K; TT: 45db - 10GHz
- **Shell continuity:**
 - . 8LT: . Z; B: 2.5mΩ
 - . . F: 1mΩ
 - . 8ST: . Z; B: 2.5mΩ
 - . . F: 1mΩ
 - . 8D: . F; TF; S: 1mΩ
 - . . Z; ZC; W: 2.5mΩ
 - . . J; M: 3mΩ
 - . . JVS: 5mΩ
 - . . TT; K: 10mΩ

Environmental

- **Temperature range:** -55°C +125°C
- **Sealing (initial):** 10^{-7} atm.cm³/s
- **Salt spray:**
 - . 8LT: . B; Z: 500h
 - . . F: 48h
 - . 8ST: . B; Z: 500h
 - . . F: 48h
 - . 8D: . F; S; TF: 48h
 - . . Z; W; JVS; TT; K; S: 500h
 - . . J; M: 2000h

Contact layouts

For C or L contact type. For other contact type or layouts, please consult us.



For further information contact us at technical.emear@souriau.com (Europe - Asia - Africa)
technical.americas@souriau.com (North America)
 or visit our web site www.souriau.com