

| SIGN                                           | DATE     | DESCRIPTION                                          | APPROVER |
|------------------------------------------------|----------|------------------------------------------------------|----------|
| △                                              | 6/24'06  | Torque standard is changed from 3.5Lb-In to 1.7Lb-In | Marvin   |
| △                                              | 11/08'08 | Body 加壓設計變更                                          | Jacke    |
| THIS IS CAD DRAWING, DO NOT REVISE MANUALLY!!! |          |                                                      |          |

### Material



- Item a Clamp: Brass(CuZn) Ni plated
- Item b Terminal screw: Steel Zinc plating “-” slot type
- Item c Female contact: PhBz, Tin or Au plated.
- Item d Terminal(housing): Thermoplastic (UL94V-0)

### Electrical


- Voltage rating: 300VAC
- Current rating: 10A
- Wire range:
- Solid wire(AWG): 16-22
- Stranded wire(AWG): 16-22
- △ Torque(Lb-In): 1.7
- Screw: M3
- Wire strip length: 5-6mm
- Withstanding Voltage: 1.6KV
- Operating temperature: -40°C to +115°C
- Safety approval: 

TT xx 01 x 0 xxxx G

|     |             |   |                   |                                                                        |                   |              |
|-----|-------------|---|-------------------|------------------------------------------------------------------------|-------------------|--------------|
| 02  | 2 CONTACTS  | 0 | Black (RAL9005)   | 0000                                                                   | Standard @ Logo   | RoHS         |
| 03  | 3 CONTACTS  | 2 | Red (RAL3001/D)   | 000A                                                                   | Standard ANY Logo | Pb<40,000ppm |
| ... | ...         | 3 | Orange(RAL2011/P) | Any special item by customer request, please contact sales department. |                   |              |
| 24  | 24 CONTACTS | 4 | Yellow(RAL1018/A) |                                                                        |                   |              |
|     |             | 5 | Green(RAL6018/T)  |                                                                        |                   |              |
|     |             | 6 | Blue (RAL5015/A)  |                                                                        |                   |              |
|     |             | 8 | Grey(RAL7035/D)   |                                                                        |                   |              |



N=Number of contacts



Section C-C


N = Number of poles  
Dim A=Nx5.0  
Dim B=(N-1)x5.0

|        | Dim A | Dim B |
|--------|-------|-------|
| 2-6p   | ±0.15 | ±0.10 |
| 7-12p  | ±0.25 | ±0.15 |
| 13-18p | ±0.30 | ±0.20 |
| 19-24p | ±0.40 | ±0.30 |

**ANYTEK**

### CUSTOMER COPY

ALL RIGHTS RESERVED. REPRODUCTION OR ISSUE TO THIRD PARTIES IN ANY FORM WHATEVER IS NOT PERMITTED WITHOUT WRITTEN AUTHORITY FROM THE PROPRIETOR. PROPERTY OF ANYTEK TECHNOLOGY CO., LTD

|          |                                  |                      |                      |                                                                                       |              |  |            |
|----------|----------------------------------|----------------------|----------------------|---------------------------------------------------------------------------------------|--------------|--|------------|
| TITLE    | TT - 5.0mm Series Stackable type |                      |                      |                                                                                       |              |  |            |
| PART NO. | TTxx01x0xxxxG                    |                      |                      | DWG NO.                                                                               | 8TT0001      |  |            |
| APPROVED | CHECKED                          | DESIGNED             | DRAWN                | CUST NO.                                                                              |              |  |            |
|          | Marvin<br>2006.08.30             | Marvin<br>2006.08.30 | Marvin<br>2006.10.04 |  | UNIT: mm     |  | X. ±0.50   |
|          |                                  |                      |                      |                                                                                       | SCALE: NONE  |  | X.X ±0.30  |
|          |                                  |                      |                      |                                                                                       | SHEET: 01/01 |  | X.XX ±0.10 |
|          |                                  |                      |                      |                                                                                       | REV.: E      |  | X° ±1°     |