




ROHS



技术要求:

- 1、天线端子主要技术指标:
 - 1) 额定负荷: 24V/0.5A
 - 2) 接触电阻: $\leq 30\text{m}\Omega$
 - 3) 绝缘电阻: $\geq 500\text{M}\Omega$
 - 4) 插入力: $\leq 50\text{N}$
- 2、天线端子主要技术指标:
 - 5) 拔出力: $\geq 1\text{N}$
 - 6) 耐压: 500V/60s
 - 7) 寿命: 500次
 - 7) 耐焊接热:
 - 人工焊: $3\text{s} \pm 0.5\text{s}$ $350^\circ\text{C} \pm 5^\circ\text{C}$
 - 自动焊: $3\text{s} \pm 0.5\text{s}$ $260^\circ\text{C} \pm 5^\circ\text{C}$
 - 8) 工作温度: $-20^\circ\text{C} \sim +75^\circ\text{C}$
- 2、天线端子不能松动。
- 3、该产品要求表面平整、清洁,不得扭曲。
- 4、该产品表面不得有划伤等缺陷。
- 5、该产品边缘不得有毛边。
- 6、未标注尺寸公差 $\pm 0.15\text{mm}$

5	上盖	1	马口铁	—	
4	围框	1	马口铁	—	
3	绝缘体	1	PPA	—	棕色
2	信号针	1	H62铜	镀锡	—
1	螺纹头	1	锌合金(压铸)	镀镍锡	
序号	名称	数量	材质	电镀	备注

浙江富港电子有限公司

浙江富港电子有限公司											
IF天线插座				图							
图样标记		重量比例									
共 页		第 页		IF-2414TA-4, 4							
审核		欧 丰	日期	21.12.15							
工 艺			日期								
校 对		李攀进	日期	21.12.15	审 定						
设 计		戴龙平	日期	21.12.15	标 准 化						
标 记		处 数			更改文件号						
						签 字					
		</									