





| SIGN                                           | DATE       | DESCRIPTION          | APPROVER |
|------------------------------------------------|------------|----------------------|----------|
| △                                              | 2010.03.10 | Add the 2p mark      | Jacke    |
| △                                              | 2010.03.10 | Added cULus standard | Jacke    |
| THIS IS CAD DRAWING, DO NOT REVISE MANUALLY!!! |            |                      |          |



Dim.A = (N-1) x 7.5+5.5  
Dim.B = (N-1) x 7.5  
N= number of poles

| poles<br>Dim. | 2P-6P | 7P-12P | 13P-16P |
|---------------|-------|--------|---------|
| Dim.A         | ±0.15 | ±0.30  | ±0.40   |
| Dim.B         | ±0.15 | ±0.30  | ±0.40   |

### Material

- Item (a) Clamp: Brass(CuZn) Ni plated
- Item (b) Terminal screw: Steel Zinc plating "-" slot type
- Item (c) Female contact: PhBz ,Tin plated
- Item (d) Terminal Cover: Thermoplastic (UL94V-0)
- Item (e) Terminal housing: Thermoplastic (UL94V-0)

### Electrical cULus

- Voltage rating: 300VAC
- Current rating: 20A
- Wire range:
- Solid wire(AWG): 12-24
- Stranded wire(AWG): 12-24
- Torque: 5Lb-In
- Screw: M3
- Wire strip length: 7-8mm
- Withstanding Voltage: 1.6KV
- Operating temperature: -40°C to +115°C
- Safety Approval:

TJ xx A1x 0 xxxx G

02 2 CONTACTS  
03 3 CONTACTS  
... ..  
16 16 CONTACTS

0 Black (RAL9005)  
2 Red (RAL3001/D)  
3 Orange(RAL2011/P)  
4 Yellow(RAL1018/A)  
5 Green(RAL6018/T)  
6 Blue (RAL5015/A)  
8 Grey(RAL7035/D)

RoHS  
Pb<40,000ppm

000 0 Standard @ Logo  
000 A Standard ANY Logo  
Any special item by  
customer request,  
please contact sales  
department.

# ANYTEK

## CUSTOMER COPY

ALL RIGHTS RESERVED. REPRODUCTION OR ISSUE TO THIRD PARTIES IN ANY FORM WHATEVER IS NOT PERMITTED WITHOUT WRITTEN AUTHORITY FROM THE PROPRIETOR. PROPERTY OF ANYTEK TECHNOLOGY CO., LTD

|          |                 |                     |                     |                                                                                       |             |         |            |          |
|----------|-----------------|---------------------|---------------------|---------------------------------------------------------------------------------------|-------------|---------|------------|----------|
| TITLE    | TJ-7.5mm Series |                     |                     |                                                                                       |             |         |            |          |
| PART NO. | TJxxA1x0xxxxG   |                     |                     |                                                                                       | DWG NO.     | 8TJ0801 |            |          |
| APPROVED | CHECKED         | DESIGNED            | DRAWN               | CUST NO.                                                                              |             |         | Tolerance  |          |
|          |                 | Jacke<br>2010.03.10 | Jacke<br>2010.03.10 |  |             |         | UNIT: mm   | X. ±0.50 |
|          |                 |                     |                     |                                                                                       | SCALE: NONE |         | X.X ±0.30  |          |
|          |                 |                     |                     | SHEET: 01/01                                                                          | REV.: C     |         | X.XX ±0.10 |          |
|          |                 |                     |                     |                                                                                       |             |         | X° ±1°     |          |