








RoHs

2.00 ± 0.15 (PITCH)




Technical Index:
1. Temperature range: $-25^{\circ}\text{C} \sim 85^{\circ}\text{C}$.
2. Rated voltage: 200V DC/AC(rms).
3. Rated current: 2.0A.
4. Contact resistance: $\leq 25\text{m}\Omega$.
5. Withstanding voltage: 500V AC/minute.
6. Insulation resistance: $\geq 1000\text{M}\Omega$.




SECTION A-A

Part No	Pin	A	B
W2001100-2PR2123	2	2.00	6.00
W2001100-3PR2123	3	4.00	8.00
W2001100-4PR2123	4	6.00	10.00
W2001100-5PR2123	5	8.00	12.00
W2001100-6PR2123	6	10.00	14.00
W2001100-7PR2123	7	12.00	16.00
W2001100-8PR2123	8	14.00	18.00
W2001100-9PR2123	9	16.00	20.00
W2001100-10PR2123	10	18.00	22.00
W2001100-11PR2123	11	20.00	24.00
W2001100-12PR2123	12	22.00	26.00
W2001100-13PR2123	13	24.00	28.00
W2001100-14PR2123	14	26.00	30.00
W2001100-15PR2123	15	28.00	32.00
W2001100-16PR2123	16	30.00	34.00
W2001100-17PR2123	17	32.00	36.00
W2001100-18PR2123	18	34.00	38.00
W2001100-19PR2123	19	36.00	40.00
W2001100-20PR2123	20	38.00	42.00



适用线路板 (PCB LAYOUT)

GENERAL TOLERANCES UNLESS SPECIFIED		 深圳市华明通电子有限公司 Shenzhen Huamingtong Electronics Co., Ltd		
X. [°] ±0.50	X. [°] ±5°	PART NO. W2001100-XPR2123	TITLE: PH2.0 弯针	
X.X [°] ±0.20	X.X [°] ±3°		CUSTOMER	SIZE A4
X.XX [°] ±0.10	X.XX [°] ±1°	DESIGN: James		UNITS MM
MANUFACTURE DWG		CHED: Talen		SCALE N:A
		APPD: Sophia		SHEET 1/1