





DIM A	$N \times 10.0 + 3.5$
DIM B	$(N-1) \times 10.0$
DIM C	$(N+2) \times 10.0$

Poles \ Tol.	Dim A&B&C
4p	± 0.20
5-10p	± 0.30
11-24p	± 0.40
25-30p	± 0.50



SIGN	DATE	DESCRIPTION	APPROVER
△	3/30'09	Structure changed	JODY
△	3/30'09	Temperature changed from -40~105℃ to -40~115℃	JODY
△	11/13'12	Change the screw plating specification	Jacky
△	11/13'12	Change the dimensional tolerance	Jacky
THIS IS CAD DRAWING, DO NOT REVISE MANUALLY!!!			

MATERIALS ELECTRICAL	
RATED VOLTAGE & CURRENT:	300 V, 20 A
WITHSTAND VOLTAGE:	AC 2000 V/Min
INSULATION RESISTANCE:	1000 MΩ OR MORE AT DC 500 V
OPERATING TEMPERATURE RANG:	△ -40 °C ~+115 °C
SCREW TORQUE VALUE:	12Lb-In.
WIRE RANGE:	22 - 12 AWG
1) MOLDED PARTS:	POLYIMIDE 66, UL 94 V-0 BLACK
2) TERMINAL:	BRASS, 0.8†, Tin PLATED
3) TERMINAL SCREWS:	STEEL, M3.5

APPROVAL:  C. A. L. S.
Critical dimension: 
PART No.:

YK 603 xx 3 x x 00G

NO. OF POLES -
04: 4 POLES
05: 5 POLES
06: 6 POLES

30: 30 POLES

└ G:RoHS compliant(lead<4%)
in copper alloy

- 0: "@" MARK
- 1: "ANY" MARK

— TERMINAL & SCREW PLATED

0: TERMINAL & SCREW: G/F
 1: TERMINAL: G/F, SCREW: Zinc
 2: TERMINAL: Sn, SCREW: G/F
 3: TERMINAL: Sn, SCREW: Zinc

ANYTEK

CUSTOMER COPY

ALL RIGHTS RESERVED. REPRODUCTION OR ISSUE TO THIRD PARTIES IN ANY FORM WHATEVER IS NOT PERMITTED WITHOUT WRITTEN AUTHORITY FROM THE PROPRIETOR. PROPERTY OF ANYTEK TECHNOLOGY CO., LTD

TITLE	YK-603 With Flange&W/O Cover Series(4-30P)						
PART NO.	YK603xx3xx00G			DWG NO.	8YK0003-603		
APPROVED	CHECKED	DESIGNED	DRAWN	CUST NO.			Tolerance
		Jacky 2012.11.13	Jacky 2012.11.13		UNIT: mm	X. ±0.50	
					SCALE: NONE	X.X ±0.30	
					SHEET: 01/01	REV.: D	X.XX ±0.10
						X° ±1°	