



N=Number of contacts



RECOMMENDED PCB LAYOUT



N = Number of poles
 Dim L=Nx5.0
 Dim P=(N-1)x5.0

	Dim L	Dim P
2-6p	±0.20	±0.15
7-12p	±0.25	±0.20
13-18p	±0.30	±0.25
19-24p	±0.40	±0.30

SIGN	DATE	DESCRIPTION	APPROVER
△	9.11'02	Added the dimension 4.4.	Shi Jun
△	9.11'02	Added the dimension 12.1.	Shi Jun
△	11.01'05	Standard spec is changed.	Marivn
△	03.08'10	Standard spec is changed.	JX0

THIS IS CAD DRAWING, DO NOT REVISE MANUALLY!!!

Material

- Terminal body
- (metal housing): Brass (CuZn)
- Terminal screw: Steel Zinc plating “-” slot type
- Wire guard: Stainless steel
- Surface of solder tail: Tin plated
- Insulator (housing): Thermoplastic (UL94V-0)

△△ Electrical cULus

- Voltage rating: 300VAC
- Current rating: 15A
- Wire range:
- Solid wire(AWG): 14-22
- Stranded wire(AWG): 14-22
- Torque(Lb-In): 3.5
- Screw: M3
- Wire strip length: 6-7mm
- Withstanding Voltage: 1.6KV
- Operating temperature: -40°C to +115°C
- Soldering temperature: 250°C±10°C/5 Sec
- Safety Approval: cULus

TQ xx 01 x 0 0000 G

02 2 CONTACTS 0 Black RoHS
 03 3 CONTACTS 5 Green Pb<40,000ppm
 6 Blue
 24 24 CONTACTS 8 Grey

ANYTEK			CUSTOMER COPY					
ALL RIGHTS RESERVED. REPRODUCTION OR ISSUE TO THIRD PARTIES IN ANY FORM WHATEVER IS NOT PERMITTED WITHOUT WRITTEN AUTHORITY FROM THE PROPRIETOR. PROPERTY OF ANYTEK TECHNOLOGY CO., LTD								
TITLE		TQ-5.0 SERIES SOLID BLOCK SERIES						
PART NO.	TQxx01x0000G		DWG NO.	8TQ0001				
APPROVED	CHECKED	DESIGNED	DRAWN	CUST NO.	Tolerance			
		xionghaitao 2006.02.04	xionghaitao 2006.02.04		X. ±0.50			
					X.X ±0.30			
					X.XX ±0.10			
					X° ±1°			
SHEET:	01/01		REV.:	D				