






- 1 MATERIAL: 15% FIBERGLASS REINFORCED PBT  
COLOR: GRAY

2 MATERIAL: 15% FIBERGLASS REINFORCED PBT  
COLOR: (SEE TABLE)

3 MATERIAL: SILICONE  
COLOR: RUST

4. RECOMMENDED WIRE DIAMETER RANGE IS 1.30  
TO 2.54mm.

5. RECOMMENDED BACKSHELLS:

STRAIGHT EXIT

A. 2292861-1 SMOOTH WIRE EXIT

B. 2292861-2 NC12/NW10 CONDUIT WIRE EXIT

C. 2292861-3 NC08/NW7.5 CONDUIT WIRE EXIT

90° EXIT


D. 2302482-1 SMOOTH WIRE EXIT

E. 2302482-2 NC12/NW10 CONDUIT WIRE EXIT

F. 2302482-3 NC08/NW7.5 CONDUIT WIRE EXIT

6. RECOMMENDED SEAL PLUG: 776363-1

7. MATING CONNECTOR: 2320933-X.



|     |           |             |
|-----|-----------|-------------|
| D   | ORANGE    | 2320927-4   |
| C   | PURPLE    | 2320927-3   |
| B   | BLUE      | 2320927-2   |
| A   | TAN       | 2320927-1   |
| KEY | TPA COLOR | PART NUMBER |

THIS DRAWING IS A CONTROLLED DOCUMENT.

DIMENSIONS:  
mm

TOLERANCES UNLESS OTHERWISE SPECIFIED:  
0 PLC ±  
1 PLC ±  
2 PLC ±0.30  
3 PLC ±  
4 PLC ±  
ANGLES ±  
FINISH -

DWN J MCNEAL 08NOV2017  
CHK R BALTER 08NOV2017  
APVD R BALTER 08NOV2017

PRODUCT SPEC  
108-2184  
APPLICATION SPEC  
114-13065  
WEIGHT 10g

Customer Drawing

TE Connectivity

NAME  
CAP ASSEMBLY, 3 POSITION,  
REDUCED DIA SEAL, HIGH TEMP,  
AMPSEAL 16

SIZE A2  
CAGE CODE 00779  
DRAWING NO C-2320927

RESTRICTED TO  
-  
SCALE 4:1  
SHEET 1 OF 1  
REV A1