




SECTION P-P

N= Number of poles
Dim.B= (N-1)x12.7
Dim.L= (N-1)x12.7+15.24

POLE	2P~8P	9P~14P	15P~20P
Dim.B	±0.20	±0.30	±0.40
Dim.L	±0.30	±0.40	±0.60

SIGN	DATE	DESCRIPTION	APPROVER
△	2/24'09	The Withstand Vol changed from 2000V/min to 2500V/min	Kind
△	2/23'11	Add approval "cULus"	Tason
△	2/23'11	Screw torque value changed from 18Kgf.cm to 16lb-In	Tason
△	5/07'12	Add the description of "first pole"	Guoxue
△	5/07'12	Add the "TOP VIEW"	Guoxue

THIS IS CAD DRAWING, DO NOT REVISE MANUALLY!!!

MATERIALS ELECTRICAL

RATED VOLTAGE & CURRENT:

600 V, 45A

△ WITHSTAND VOLTAGE:

AC 2500 V/Min

INSULATION RESISTANCE:

1000 MΩ OR MORE AT DC 500 V

OPERATING TEMPERATURE RANG:

-40 °C ~ +115 °C

△ SCREW TORQUE VALUE:

16lb-In

WIRE RANGE:

18 - 8 AWG

1) BODY:

THERMOPLASTICS, UL94-V0 BLACK

2) TERMINAL:

BRASS, 1.6t, Tin PLATED

3) TERMINAL SCREWS WITH WASHER:

STEEL, Ni PLATED, M4.0

△ APPROVAL: 

Critical dimension: 

NO. OF POLES

02: 2 POLES

03: 3 POLES

04: 4 POLES

...

20: 20 POLES

YK 881 xx 0 x x 00G

G RoHS compliant
(lead<4%)
In copper Alloy

MARK

0: "@" MARK

1: "ANY" MARK

TERMINAL & SCREW PLATED

0: TERMINAL & SCREW: G/F

1: TERMINAL: G/F, SCREW: Ni

2: TERMINAL: Sn, SCREW: G/F

3: TERMINAL: Sn, SCREW: Ni

ANYTEK

CUSTOMER COPY

ALL RIGHTS RESERVED. REPRODUCTION OR ISSUE TO THIRD PARTIES IN ANY FORM WHATEVER IS NOT PERMITTED WITHOUT WRITTEN AUTHORITY FROM THE PROPRIETOR. PROPERTY OF ANYTEK TECHNOLOGY CO., LTD

TITLE		YK881 SERIES			
PART NO.	YK881xx0xx00G			DWG NO.	8YK0001-881
APPROVED	CHECKED	DESIGNED	DRAWN	CUST NO.	
		Guoxue 2012.05.07	Guoxue 2012.05.07		
				UNIT: mm	X. ±0.50
				SCALE: NONE	X.X ±0.30
				SHEET: 01/01	X.XX ±0.10
				REV.: D	X° ±1°