

4

3




2

1

used for:

D-SUB

POS.	A ^{-0.76}	B ^{+0.25}	C	D ^{-0.3}	Part-NO.
9	31.19	16.79	25.00 ^{+0.12/-0.13}	6.12	163A17379X
15	39.52	25.12	33.30 ^{+0.15/-0.1}	6.12	163A17389X
25	53.42	38.84	47.04 ^{±0.13}	5.99	163A17399X
37	69.70	55.30	63.50 ^{±0.13}	5.99	163A17409X




Directive 2002/95/EC
„RoHS“
Compliant


NOTES:

1. METALSHELLS: STEEL; min. 315µin TIN over 40-80µin NICKEL
2. INSULATORS: PBT GF UL 94 V-0, BLACK
3. CONTACTS: COPPER ALLOY
PLATING: 8µin HARD GOLD OVER min. 50µin NICKEL
SOLDER CUP ACCEPTS CABLE AWG 20
4. CONNECTOR IS PART MARKED: PART-NO. CONEC ABC

APPROVAL * FREIGABE * DEBLOCAGE * AUTORIZACION * APPROVAL	
CUSTOMER APPROVAL DATE:	
NAME:	TITLE:
COMPANY NAME:	
APPROVAL * FREIGABE * DEBLOCAGE * AUTORIZACION * APPROVAL	

THIS DRAWING MAY NOT BE COPIED OR
REPRODUCED IN ANY WAY, AND MAY NOT
BE PASSED ON TO A THIRD PARTY WITHOUT
WRITTEN PERMISSION.
OWNERSHIP AND COPYRIGHT OF CONEC GmbH
DO NOT ALTER CAD DRAWING BY HAND

				tolerance		 dim. in mm
				2007	date	name
				drawn	04.01.	Lehmenkühler
				appd.	04.01.	Mickenbecker
				norm	DIN 41652	
				d-old		
a	Origin					
rev.	description	date	name			



dim. in mm

scale: 2:1
material: SEE NOTES

title:
D-SUB MALE
9-37pos. SOLDER CUP
with stamped contacts

dwg no: AutoCAD 2004 DIN-A
16K1A1955 4
sh: 1/1

part no: SEE TABLE

4

3

2

1