


Poles	03	04
Dim L	30.32	40.48
Dim B	20.32	30.48
Dim C	48.24	58.4
TOL	± 0.25	

SIGN	DATE	DESCRIPTION	APPROVER
△	04/08'09	The Voltage rating, Screw and operating temperature are changed	Jacke
△	04/08'09	The pole is changed	Jacke
△	2009.10.23	The design is changed	Jacke
△	2010.02.04	The material is changed from Brass to Copper	Jacke
△	2010.04.10	Add UL standard	Jacke
△	2010.06.07	The flange screw is changed from "-" type to "+/-" type	Cheng Bo
THIS IS CAD DRAWING, DO NOT REVISE MANUALLY!!!			

- Item a Terminal body :Thermoplastic (UL94V-0)
- Item b Terminal cover :Thermoplastic (UL94V-0)
- Item c Terminal screw :Steel Cr3+ Zinc plating “-” slot type
- Item d Clamp:Brass, Ni plated
- △ ● Item e Female contact pin :Copper Tin plated
- Item f Wire guard :Stainless Steel
- Item g With flange screw :Steel Zinc plating M3“+/-”slot type
- Item h With steel holder :Steel Zinc plating
Electrical cULus / IEC
- △ ● Voltage rating: 300VAC / 1000VAC
- Current rating: 55A / 76A
- Solid wire (AWG):6-20 / 0.5-16mm²
- Stranded wire(AWG): 6-20 / 0.5-16mm²
- Torque: 10.4 Lb-In / 1.2 N.m
- △ ● Screw: M4.5
- Wire strip length: 13-14mm
- Withstanding Voltage: 1.6KV / 8KV
- △ ● Operating temperature: -40°C to +115°C
- △ ● Safety approval: cULus

				RoHS	
				Pb<40,000ppm	
Poles		Color		0000 Standard @ Logo	
03	3Contacts	0	Black (RAL9005)	000A Standard ANY Logo	
04	4Contacts	2	Red (RAL3001/D)	Any special item by customer request, please contact sales department.	
		3	Orange(RAL2011/P)		
		4	Yellow(RAL1018/A)		
		5	Green(RAL6018/T)		
		6	Blue (RAL5015/A)		
		8	Grey(RAL7035/D)		

ANYTEK

CUSTOMER COPY

ALL RIGHTS RESERVED. REPRODUCTION OR ISSUE TO THIRD PARTIES IN ANY FORM WHATEVER IS NOT PERMITTED WITHOUT WRITTEN AUTHORITY FROM THE PROPRIETOR. PROPERTY OF ANYTEK TECHNOLOGY CO., LTD

TITLE	EV 10.16 Series 3~4p (W/F) With handle						
PART NO.	EVxx61x2xxxxG			DWG NO.	8EV0003		
APPROVED	CHECKED	DESIGNED	DRAWN	CUST NO.			Tolerance
			Cheng Bo 2010.06.07		UNIT: mm	X. ±0.50	
					SCALE: NONE	X.X ±0.30	
				SHEET: 01/01	REV.: G	X.XX ±0.10	
						X° ±1°	