






VER	MARK	PR. BY	DESCRIPTTON	DATE



<i>Part No</i>	<i>Pin</i>	<i>A</i>	<i>B</i>
<i>W396111K-2PY2123</i>	<i>2</i>	<i>3. 96</i>	<i>7. 92</i>
<i>W396111K-3PY2123</i>	<i>3</i>	<i>7. 92</i>	<i>11. 88</i>
<i>W396111K-4PY2123</i>	<i>4</i>	<i>11. 88</i>	<i>15. 84</i>
<i>W396111K-5PY2123</i>	<i>5</i>	<i>15. 84</i>	<i>19. 80</i>
<i>W396111K-6PY2123</i>	<i>6</i>	<i>19. 80</i>	<i>23. 76</i>
<i>W396111K-7PY2123</i>	<i>7</i>	<i>23. 76</i>	<i>27. 72</i>
<i>W396111K-8PY2123</i>	<i>8</i>	<i>27. 72</i>	<i>31. 68</i>
<i>W396111K-9PY2123</i>	<i>9</i>	<i>31. 68</i>	<i>35. 64</i>
<i>W396111K-10PY2123</i>	<i>10</i>	<i>35. 64</i>	<i>39. 60</i>
<i>W396111K-11PY2123</i>	<i>11</i>	<i>39. 60</i>	<i>43. 56</i>
<i>W396111K-12PY2123</i>	<i>12</i>	<i>43. 56</i>	<i>47. 52</i>
<i>W396111K-13PY2123</i>	<i>13</i>	<i>47. 52</i>	<i>51. 48</i>
<i>W396111K-14PY2123</i>	<i>14</i>	<i>51. 48</i>	<i>55. 44</i>
<i>W396111K-15PY2123</i>	<i>15</i>	<i>55. 44</i>	<i>59. 40</i>
<i>W396111K-16PY2123</i>	<i>16</i>	<i>59. 40</i>	<i>63. 36</i>




适用线路板 (PCB LAYOUT)

序号	品名	材质
1	VH3. 96 胶芯	PA66 UL94V-2 Yellow
2	VH3. 96 直针端子	Copper Alloy/ Tin Plating

Technical Index:

1. Temperature range: $-25^{\circ}\text{C}\sim 85^{\circ}\text{C}$.
2. Rated voltage: 250V DC/AC(rms).
3. Rated current: 7.0A.
4. Contact resistance: $\leq 20\text{m}\Omega$.
5. Withstanding voltage: 1500V AC/minute.
6. Insulation resistance: $\geq 1000\text{M}\Omega$.

GENERAL TOLERANCES UNLESS SPECIFIED		 深圳市华明通电子有限公司 Shenzhen Huamingtong Electronics Co., Ltd			
X.° ±0.50	X.° ±5°	PART NO.		TITLE:	
X.X° ±0.20	X.X° ±3°	W396111K-XPY2123		VH3.96 直针	
X.XX°±0.10	X.XX° ±1°	DESIGN: James	CUSTOMER	SIZE	UNITS
MANUFACTURE DWG		CHED: Talen		A4	MM
		APPD: Sophia		SCALE	SHEET
				N:A	1/1