



LOC HB	DIST	REVISIONS							
		P	LTR	DESCRIPTION		DATE	DWN	APVD	
			B1	1.CHANGE TE LOGO 2.ADD LINE IDENTIFICATION 3.PIN OBSOLETE 4.TERMINALS TOLERANCE CLARIFICATION		ECO-11-018616	03-MAY-12	P.L	BH.Y



GENERAL TOLERANCE



Diagram dimension	Tolerance
0.99mm max.	±0.1mm
1 - 2.99mm	±0.2mm
3mm min.	±0.3mm

NOTE:
1.LOT NO. SYSTEM AS FOLLOWING:



B1 2.TERMINAL DIMENSIONS BEFORE SOLDER DIP


B1 3.FOR THE TIN-PLATING OF THE PINS:
+0.1mm FOR WIDTH, THICKNESS AND DIAMETER
+0.5mm FOR LENGTH




DIMENSIONS: mm		DWN	ZHUAN,ZHOU	TE Connectivity	
		CHK	BANGHUA,YU		
	TOLERANCES UNLESS OTHERWISE SPECIFIED: 0 PLC ± 1 PLC ± 2 PLC ± 3 PLC ± 4 PLC ±	APVD	SUUNY ZHANG	T81 H/N CUSTOMER DRAWING	
		PRODUCT SPEC	_____		
		APPLICATION SPEC	_____		
		WEIGHT	_____	SIZE	A3
MATERIAL	FINISH	_____	_____	GAGE CODE	_____
SEE MATERIAL TABLE	_____	_____	_____	DRAWING NO	1393779
RESTRICTED DRAWING				RESTRICTED TO	_____
SCALE 4:1				SHEET 1 OF 2	REV B1

LOC HB	DIST	REVISIONS						
		P	LTR	DESCRIPTION	ECN	DATE	DWN	APVD

PC Board Layout(Bottom View)



WIRING DIAGRAM (BOTTOM VIEW)



ACTIVE	6-1393779-9	T81N5D312-05	5V	T81N5D312-05	i
ACTIVE	7-1393779-2	T81N5D312-24	24V	T81N5D312-24	h
ACTIVE	7-1393779-1	T81N5D312-12	12V	T81N5D312-12	g
OBSOLETE	7-1393779-0	T81N5D312-09	9V	T81N5D312-09	f
ACTIVE	5-1393779-9	T81H5D312-24	24V	T81H5D312-24	e
ACTIVE	5-1393779-8	T81H5D312-12	12V	T81H5D312-12	d
OBSOLETE	5-1393779-7	T81H5D312-09	9V	T81H5D312-09	c
OBSOLETE	5-1393779-6	T81H5D312-06	6V	T81H5D312-06	b
ACTIVE	5-1393779-5	T81H5D312-05	5V	T81H5D312-05	a
STATUS	PART NO	DECRPTION	PART B	PART A	ITEM

B1

		UV	SEAL (FOR SEALED TYPE)	15
		SEAL GLUE	SEAL (CASE & BASE)	14
		3UEW	MAGNETIC WIRE	13
		HCP WIRE	COIL TERMINAL	12
		Aq ALLOY	B CONTACT	11
		Aq ALLOY	M CONTACT	10
		Aq ALLOY	MOVABLE CONTACT	9
		Cu ALLOY	B TERMINAL	8
		Cu ALLOY	M TERMINAL	7
		Cu ALLOY	MOVABLE SPRING	6
UL94V-0		PBT	BOBBIN	5
UL94V-0		PBT	CASE	4
		CSC C	CORE	3
	CuNi PLATING	SPCC	ARMATURE	2
	CuNi PLATING	SPCC	YOKE	1
INCOMBUSTIBILITY	TREATMENT	MATERIAL	DESCRIPTION	ITEM

DIMENSIONS: mm		TOLERANCES UNLESS OTHERWISE SPECIFIED: 0 PLC ± 1 PLC ± 2 PLC ± 3 PLC ± 4 PLC ±		DWN ZHUAN,ZHOU	TE Connectivity			
				CHK BANGHUA,YU				
		MATERIAL SEE MATERIAL TABLE		APVD SUUNY ZHANG	T81 H/N CUSTOMERT DRAWING			
				PRODUCT SPEC _____				
FINISH _____		WEIGHT _____		APPLICATION SPEC _____	SIZE A3	GAGE CODE _____	DRAWING NO C- 1393779	RESTRICTED TO _____
				RESTRICTED DRAWING	SCALE 4:1	SHEET 2 OF 2	REV B1	