




LOC	DIST	REVISIONS					
DY	-	P	LTR	DESCRIPTION	DATE	DWN	APVD
			A	RELEASED FOR PRODUCTION	30DEC2015	TX	SH




NOTES:


- 1 MATERIAL:
HOUSING: HIGH TEMP THERMOPLASTIC, UL94V-0,
COLOR:BLACK
CONTACT:COPPER ALLOY
BOARDLOCK:COPPER ALLOY
- 2 FINISH:
CONTACT AREA:
MIN 0.76 μ m GOLD PLATING
SOLDERTAIL: MIN 2.54 μ m MATTE TIN PLATING
UNDERPLATE: MIN 1.27 μ m NICKEL PLATING
- 3 PIN #P4 AND #P12 ONLY
- 4 SOLDERTAIL TO BE 0.05 MAX ABOVE
AND 0.10 MAX BELOW DATUM E
- 5 1.33 MAX MEASURED AT DATUM C



SECTION H - H
SCALE 4:1




DETAIL A
SCALE 8:1



TRAY	YES	2170518-3
TAPE & REEL	YES	2170518-2
TRAY	NO	2170518-1
PACKAGING	PICK-UP CAP (1)	PART NUMBER

THIS DRAWING IS A CONTROLLED DOCUMENT.		DWN BING LIU 10APR2013 CHR JASON YANG 10APR2013 APVD ALEX CAI 10APR2013		 TE Connectivity	
DIMENSIONS: mm		TOLERANCES UNLESS OTHERWISE SPECIFIED: 0 PLC ±. 1 PLC ±0.20 2 PLC ±0.20 3 PLC ±0.20 4 PLC ±. ANGLES ±3°		NAME 12G SAS/PCIe COMBO RECEPTACLE (WITH SMT HOLDDOWNS) 15P+7P+6P+40P	
		PRODUCT SPEC 108-51109 APPLICATION SPEC 114-60017		SIZE CAGE CODE DRAWING NO RESTRICTED TO	
MATERIAL -		WEIGHT -		A200779 C-2170518 -	
CUSTOMER DRAWING				SCALE 2:1	SHEET 1 OF 2
				REV A	



THIS DRAWING IS A CONTROLLED DOCUMENT.

DWN BING LIU 10APR2013

CHK JASON YANG 10APR2013

APVD ALEX CAI 10APR2013

DIMENSIONS:

mm

TOLERANCES UNLESS OTHERWISE SPECIFIED:

0 PLC ±-

1 PLC ±0.20

2 PLC ±0.20

3 PLC ±0.20

4 PLC ±

ANGLES ±3°

FINISH

PRODUCT SPEC

108-51109

APPLICATION SPEC

114-60017

WEIGHT

CUSTOMER DRAWING

NAME

12G SAS/PCIe COMBO RECEPTACLE (WITH SMT HOLDDOWNS) 15P+7P+6P+40P

SIZE

CAGE CODE

DRAWING NO

RESTRICTED TO

A200779

C-2170518

SCALE 2:1

SHEET 1 OF 2

REV A