






PART No.	CODE No.	A	B
DF5A-4DP-5DSA (35)	CL676-0029-0-35	-	12.5
DF5A-6DP-5DSA (35)	CL676-0030-0-35	10.0	17.5
DF5A-8DP-5DSA (35)	CL676-0031-2-35	15.0	22.5
DF5A-10DP-5DSA (35)	CL676-0032-5-35	20.0	27.5
DF5A-12DP-5DSA (35)	CL676-0033-8-35	25.0	32.5
DF5A-14DP-5DSA (35)	CL676-0034-0-35	30.0	37.5
DF5A-16DP-5DSA (35)	CL676-0035-3-35	35.0	42.5




APPLICATION DIAGRAM



RECOMMENDED PCB LAYOUT (t=1.6±0.1)



			2		BRASS		SURFACE:TIN PLATED 1μm min UNDER PLATING:NICKEL PLATED 0.5μm min													
1	POLYAMIDE		NATURAL (BEIGE)・UL94V-0																	
NO.		MATERIAL		FINISH , REMARKS			NO.		MATERIAL		FINISH , REMARKS									
UNITS mm				SCALE 2 : 1				COUNT	DESCRIPTION OF REVISIONS			DESIGNED		CHECKED		DATE				
 HIROSE ELECTRIC CO., LTD.				APPROVED : KI. AKIYAMA				15.08.08		DRAWING NO.		EDC-302829-35-01								
				CHECKED : TS. FUKUSHIMA				15.08.08		PART NO.		DF5A-*DP-5DSA(35)								
				DESIGNED : TS. KUMAZAWA				15.08.08		CODE NO.		CL676								
				DRAWN : TS. KUMAZAWA				15.08.08												
																			1/1	