


REVISIONS			
LTR	DESCRIPTION	DATE	APPROVED
N/C	INITIAL RELEASE PER DCR# T-24384	3/2/2000	M.HIGGY
A	REVISE PER DCR# T-29844	8/17/2001	M.HIGGY



PLUG ASSEMBLY

RECEPTACLE ASSEMBLY

SPECIFICATION CONTROL DRAWING

NOTES: SEE SHEET 2.

If this document is printed it becomes uncontrolled.
Check with the web for latest revision.

UNLESS OTHERWISE SPECIFIED DIMENSIONS ARE IN INCHES. METRIC DIMENSIONS ARE IN BRACKETS. DECIMALS .XXX ±.005 { .13 mm } .XX ±.02 { .5 mm } ANGLES .X ± WEIGHT: 8	DRAWN	ZS.ORBAN	2/29/2000	tyco / Electronics / Raychem WIRE AND HARNESSING PRODUCTS 307 CONSTITUTION DRIVE MENLO PARK, CALIFORNIA 94025					
	CHECKED								
	APPROVED			TITLE SHELL, PLUG OR RECEPTACLE, SPECIAL MARKING, 1" AND 2" WITH EARS, CADMIUM PLATED					
	APPROVED	M.HIGGY	3/2/2000						
	CAD NAME	T29844a,b,DWG			SIZE C	CODE IDENT. NO. 06090	DWG. NO. MTCCXX-YYYYYY-01	1	REV A
	THIRD ANGLE PROJECTION								
					DO NOT SCALE THIS DRAWING			SHEET 1 OF 2	

SHEET 1
MTCCXX-YYYYY-01
DWG. NO.

If this document is printed it becomes uncontrolled.
Check with the web for latest revision.

NOTES:

1 PART NUMBER VARIABLES:

MTCCXX-YYYYYY-01

01= WITH CABLE CLAMP

CUSTOMER SPECIFIED PART MARKING
(ANY LENGTH)

SHELL TYPES:

P= PLUG WITH EARS

R= RECEPTACLE WITH EARS

CONNECTOR WIDTH:

1= 1 INCH

2= 2 INCH

2. MATERIAL:

- | | |
|---------------------------------------|--|
| A) SHELL | ALUMINUM ALLOY PER QQ-A-591 |
| B) RETENTION CLIP | COPPER ALLOY 172 PER QQ-C-533 |
| C) ADAPTER SCREW OR CAP SCREW | STAINLESS STEEL PER QQ-S-763, 300 SERIES |
| D) ADAPTER NUT OR
RETAINER BUSHING | STAINLESS STEEL PER QQ-S-763, 300 SERIES |
| E) PANEL OR LOCK WASHER | STAINLESS STEEL PER QQ-S-763 OR QQ-S-766, 300 SERIES |
| F) KEYING PIN | HIGH GRADE POLYARYLENE THERMOPLASTIC, MOLDED |
| G) KEY PINS INSERT | HIGH GRADE POLYARYLENE THERMOPLASTIC, MOLDED |
| H) CLAMP BAR | STAINLESS STEEL PER QQ-S-763, 300 SERIES |
| J) CLAMP INSERT | SILICONE ELASTOMER PER MIL-R-25988 |
| K) CAPTIVE SCREW | STAINLESS STEEL PER QQ-S-763, 300 SERIES |
| L) RETAINING RING | COPPER ALLOY 172 PER QQ-C-533 |
| M) DUST CUP | POLYETHYLENE LOW DENSITY PER L-P-390, COLOR RED. |

3. FINISH: CADMIUM PLATED CONNECTORS

- | | |
|---------------------------------------|---|
| A) SHELL | CADMIUM PLATED PER QQ-P-416
OVER NICKEL UNDERPLATE |
| B) RETENTION CLIP | CADMIUM PLATED PER QQ-P-416 |
| C) ADAPTER OR CAP SCREW | CADMIUM PLATED PER QQ-P-416 |
| D) ADAPTER NUT OR
RETAINER BUSHING | CADMIUM PLATED PER QQ-P-416 |
| E) PANEL OR LOCK WASHER | CADMIUM PLATED PER QQ-P-416 |
| F) CLAMP BAR | CADMIUM PLATED PER QQ-P-416 |
| G) CAPTIVE SCREW | CADMIUM PLATED PER QQ-P-416 |
| H) RETAINING RING | CADMIUM PLATED PER QQ-P-416 |

4 DUST CAP SUPPLIED WITH EACH PLUG OR RECEPTACLE.

5 APPROPRIATE PART NUMBER AND DATE CODE ARE STAMPED APPROXIMATELY AS SHOWN.

6. THESE PARTS MEET THE REQUIREMENTS OF RAYCHEM SPECIFICATION C-6111.

7 INDICATED PARTS ARE SHIPPED LOOSE.

8 SEE TABLE I, WEIGHTS ARE WITHOUT DUST CAP.

TABLE I

PART NUMBER	WEIGHT MAXIMUM GRAMS
MTCC1R-YYYYYY-01	27.3
MTCC1P-YYYYYY-01	23.8
MTCC2R-YYYYYY-01	38.3
MTCC2P-YYYYYY-01	34.2