








RoHs

Part No	Pin	A	B
W254111K-2PR2123	2	2.5	7.5
W254111K-3PR2123	3	5.0	10.0
W254111K-4PR2123	4	7.5	12.5
W254111K-5PR2123	5	10.0	15.0
W254111K-6PR2123	6	12.5	17.5
W254111K-7PR2123	7	15.0	20.0
W254111K-8PR2123	8	17.5	22.5
W254111K-9PR2123	9	20.0	25.0
W254111K-10PR2123	10	22.5	27.5
W254111K-11PR2123	11	25.0	30.0
W254111K-12PR2123	12	27.5	32.5
W254111K-13PR2123	13	30.0	35.0
W254111K-14PR2123	14	32.5	37.5
W254111K-15PR2123	15	35.0	40.0
W254111K-16PR2123	16	37.5	42.5
W254111K-17PR2123	17	40.0	45.0



适用线路板 (PCB LAYOUT)

序号	品名	材质
1	HA2.5 胶芯	PA66 UL94V-2 Red
2	HA2.5 直针端子	Copper Alloy/ Tin Plating

Technical Index:

- Temperature range: $-25^{\circ}\text{C} \sim 85^{\circ}\text{C}$.
- Rated voltage: 250V DC/AC(rms).
- Rated current: 3.0A.
- Contact resistance: $\leq 20\text{m}\Omega$.
- Withstanding voltage: 1000V AC/minute.
- Insulation resistance: $\geq 1000\text{M}\Omega$.

GENERAL TOLERANCES UNLESS SPECIFIED			
X. $^{\circ}$ ± 0.50	X. $^{\circ}$ $\pm 5^{\circ}$	PART NO. W254111K-XPR2123	
X.X $^{\circ}$ ± 0.20	X.X $^{\circ}$ $\pm 3^{\circ}$	TITLE: HA2.5 直针带扣	
X.XX $^{\circ}$ ± 0.10	X.XX $^{\circ}$ $\pm 1^{\circ}$	DESIGN: James	CUSTOMER
MANUFACTURE DWG		CHED: Talen	SIZE A4
		APPD: Sophia	UNITS MM
			SCALE N:A
			SHEET 1/1