





(d) (b) NOTES:

CRIMPING:
USE CRIMP TOOL: 360X10409X
WITH TOOL INSERT: 360X20029X
SELECTOR SETTINGS: 7 FOR AWG 10
6 FOR AWG 12

plating	part no.
GOLD FLASH over NICKEL	132A11039X
30µin HARD GOLD over min. 50µin NICKEL	132C11039X
50µin HARD GOLD over min. 50µin NICKEL	132J11039X

(b) STRIPPING DIMENSIONS



RoHS compliant

3	1	RETAINING RING				COPPER ALLOY				NICKEL PLATED							
2	1	REAR SIDE				COPPER ALLOY				GOLD FLASH over NICKEL							
1	1	MATING SIDE				COPPER ALLOY				see table							
pos	qty	description				material				plating							
partlist																	
THIS DRAWING MAY NOT BE COPIED OR REPRODUCED IN ANY WAY, AND MAY NOT BE PASSED ON TO A THIRD PARTY WITHOUT WRITTEN PERMISSION. OWNERSHIP AND COPYRIGHT OF CONEC GmbH DO NOT ALTER CAD DRAWING BY HAND				tolerance				 dim. in mm		scale: 5:1							
										material: see partlist							
									date	name	title: HIGH POWER CONTACT FEMALE CRIMP VERSION 30A D-SUB COMBINATION						
								drawn	23.03.98	Barcinski							
								appd.	23.03.98	Mickenbecker							
				4 x d	Ä5877	09.11.2015	K.H.	norm				dwg no: 13K1IE9A part no: see table				DIN-A3 sh: 1	
				1 x c	Ä2197	01.04.2005	Lehm.	d-old	13K2IE9A								
				2 x b	Ä2177	02.03.2005	Lehm.										
				a	Original												
				rev.	description	date	name										